


Part Number : 622018607

Product Description : Press-In Tool for Vertical Header 7-Row, 4-Column

Series Number : 207123

Status : Obsolete

Product Category : Application Tooling Accessories



Documents & Resources

Tooling Specifications

[ATS-622018607-001.pdf](#)

[TM-622018699-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Obsolete
Category	Application Tooling Accessories
Series	207123
Description	Press-In Tool for Vertical Header 7-Row, 4-Column
Comments	See Tooling Specification (PDF) Above, Press-In Tool
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	822350874632
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Physical

Net Weight	54.910/g
------------	----------

Applicable Parts

Description	Part Number
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 4.70mm	<u>760151403</u>
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 5.70mm	<u>760151404</u>
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 3.90mm, Lead-Free	<u>760153402</u>
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 4.70mm, Lead-Free	<u>760153403</u>
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Right Guide, Left Open, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 3.90mm, Lead-Free	<u>760155402</u>
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Right Guide, Left Open, 7 Rows, 4 Columns, 56 Circuits, Mating Pin Length 4.70mm, Lead-Free	<u>760155403</u>

This document was generated on Sep 16, 2025