
All dimensions in mm	If in doubt - ask	©


Customer Information Sheet




Tape Details

Tolerance = ±0.10
(Unless Otherwise Stated)

Scale 6:1







Section Y-Y


Section X-X


Component Details:


Tolerance = ±0.15
(Unless Otherwise Stated)













Reel Details



Scale 3:20



Scale 4:5

Specification:
- Material = Phosphor Bronze, 0.15mm Thick
- Finish = Gold flash over Nickel
- Electrical:
  - Contact Resistance = 50mΩ Max
  - Current Rating = 1A
- Mechanical:
  - Durability = 10,000 Cycles
  - Minimum Force at Working Height = 0.49N
- Environmental:
  - Operating Temperature = -20°C to + 70°C

RA	6	15.12.25	37154
Initials	Rev.	Date	CO
SB	1	20.08.15	-----

Notes:
1. Quantity per reel = 2,000.
2. This product is taped and reeled in general accordance with EIA-481 (Electronics Industries Association).

HARWIN
www.harwin.com

This drawing and any information or descriptive matter set out hereon are confidential and copyright property of the Harwin group and must not be disclosed, loaned, copied or used for manufacturing, tendering or for any other purpose without their written permission.

TOLERANCES
X. = ±0.50mm
X.X = ±0.30mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
Angles = ±5°
Unless stated

Third angle projection

Sheet scale: 2:1
Do not scale
Sheet size: A3

MATERIAL: See above

FINISH: See above

Title: SMT Spring Contact (3.00mm High) in Tape and Reel

Drawing number: **S7151-45R**

SHT 2 OF 2

Downloaded from Arrow.com.