






LOCATE HOLES
 $\phi 0.13 \pm 0.005$
 POSITION DIMENSIONS
 ARE BASIC



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	NOV.06/2019	A.GREEN



RECOMMENDED PANEL CUTOUT

MATERIALS:

RJ:

HOUSING & COVER: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
 SEE AMPHENOL PART NUMBER FOR DETAIL.

50 μ [1.27 MICRONS]

MIN. NICKEL UNDERPLATE

100 μ TIN PLATING ON CONTACT TAILS.

SHIELD: STAINLESS STEEL, WITH TIN-DIP ON SOLDER TABS.

USB:

HOUSING: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0,
 COLOUR: BLUE

CONTACTS: PHOSPHOR BRONZE

PLATING: SELECTIVE GOLD FLASH ON MATING SURFACES

50 μ [1.27 MICRONS]

MIN. NICKEL UNDERPLATE

100 μ TIN PLATING ON CONTACT TAILS

SHIELD: STAINLESS STEEL WITH NICKEL.

AMPHENOL PART NUMBER: RJE36-188-2XX5

GOLD PLATING REFER TO LED
 0 = GOLD FLASH OPTION DRAWING.

1 = 6 μ INCH

2 = 15 μ INCH

3 = 30 μ INCH

4 = 50 μ INCH

UNLESS SPECIFIED OTHERWISE		DRAWN	JACK.GUO	DATE	NOV.06/2019	Amphenol Canada Corp. Commercial Products	
PRIMARY UNITS	MILLIMETER	CHECKED	L.CHAN		NOV.06/2019		
SECONDARY		M.E. APP'D				TITLE RJ45 OVER TWO USB 3.0 COMBO, DIP TYPE WITHOUT TABS, LEDS OPTIONS-RoHS COMPLIANT	
REFERENCE IN PARENTHESES		Q.A. APP'D					
GENERAL TOLERANCES		DWG APPR.	A.GREEN	DATE	NOV.06/2019	DWG. NO. P-RJE36-188-2XX5	
1 DECIMAL PLACE	± 0.30	ENG. REL. NO.					
2 DECIMAL PLACES	± 0.25	REF.				REV A	
3 DECIMAL PLACES	± 0.20	THIRD ANGLE PROJECTION					
ANGULAR DEGREES	$\pm 1.0^\circ$	DO NOT SCALE DRAWING				CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	