Part Number : 875681463
Product Description : Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp
Series Number : 87568
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

875681463_sd.pdf

PK-87568-0001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

503940002-AS-000.pdf

PS-87568-004-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	87568
Description	Milli-Grid Cable-to-Board Receptacle, Dual Row, IDT, Lead-Free, 14 Circuits, 0.38µm Gold (Au) Selective Plating, without Center Polarization Key and Locking Friction Ramp
Product Name	Milli-Grid
UPC	822348457557

Agency

CSA	LR19980
UL	E29179

Electrical

Voltage - Maximum	125V

Physical

Circuits (Loaded)	14

Downloaded from Arrow.com.

Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	Polyester
Net Weight	0.883/g
Number of Rows	2
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-45° to +105°C
Termination Interface Style	IDT or Pierce
Wire Size (AWG)	28

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Milli-Grid Vertical, Dual Row, Through Hole Headers	87831
Milli-Grid Vertical, Dual Row, Surface Mount Headers	87832
Milli-Grid Right-Angle Dual Row Through Hole Headers	87833

Use with Part(s)

Downloaded from Arrow.com.

Description	Part Number
2.00mm Strain Relief for Dual Row IDT, 14 Circuits	875691014

Application Tooling

Global

Description	Part Number
IDT - Manual - Handtool	621002000
Manual Press with IDT Ribbon Cable Tool Kit	621002200
IDT Ribbon Cable Adapter Kit for 2.00mm	621002400
IDT - Manual - Tool Kit	621003200

Downloaded from Arrow.com.