

TCP 10A - Thermal device circuit breaker



0712314

<https://www.phoenixcontact.com/us/products/0712314>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



1-channel thermal device circuit breaker for protecting loads at 250 V AC / 72 V DC in the event of an overload. For installation on fuse terminal blocks and interfaces for flat plug-in fuse of type C according to standard ISO 8820-3. With fixed nominal current: 10 A

Your advantages

- Fast, replacement part-free recommissioning after an event with the reconnection options
- Easy to retrofit in existing systems with vehicle flat-type fuses with identical pin connector pattern
- System disconnection for maintenance actions via the integrated device switch

Commercial data

Item number	0712314
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL15
Product key	CLA111
GTIN	4017918848415
Weight per piece (including packing)	11.173 g
Weight per piece (excluding packing)	11.173 g
Customs tariff number	85362010
Country of origin	ID

TCP 10A - Thermal device circuit breaker



0712314

<https://www.phoenixcontact.com/us/products/0712314>

Technical data

Notes

General	When mounted in rows, the nominal device current can be limited to just 80% or must be oversized accordingly.
---------	---

Product properties

Product type	Thermal device circuit breakers
Type	Male
Number of positions	1
No. of channels	1

Insulation characteristics

Overvoltage category	II
Degree of pollution	2

Electrical properties

Fuse type	Automatic device
Fuse	Slow-blow

General

Rated voltage	250 V AC
	65 V DC
	250 V AC (AC according to UL 1077)
	72 V DC (DC according to UL 1077)
Rated current I_N	10 A
Rated surge voltage	2.5 kV
Insulation resistance R_{iso}	> 100 M Ω (500 V DC)
Tripping method	T (thermal)
Device resistance	0.05 Ω
Rated short-circuit switching capacity I_{cn}	80 A (250 V AC / 65 V DC)
	200 A (30 V DC)
Short-circuit switching capacity	2000 A (250 V AC / UL 1077)
	2000 A (72 V DC / UL 1077)
Dielectric strength	3000 V AC (Actuation area)
	1500 V AC (Installation area)
Switching cycles, max.	6000 (At 1 x I_N , low-induction)
	3000 (At 1 x I_N , inductive)
	500 (At 2 x I_N , inductive)
Contact switching type	Type C in accordance with ISO 8820-3

Connection data

Nominal current	10 A
Nominal voltage	250 V AC
	65 V DC

TCP 10A - Thermal device circuit breaker




0712314

<https://www.phoenixcontact.com/us/products/0712314>

Connection method	pluggable
-------------------	-----------

Dimensions

Dimensional drawing



Width	8.2 mm
Height	24.4 mm
Height NS 35/7,5	55 mm
Depth	44.5 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V-0
Insulating material group	IIIb
Insulating material	PPS

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40 (Actuation area)
Ambient temperature (operation)	-20 °C ... 60 °C
Altitude	≤ 4000 m (amsl)
Humidity test	240 h, 95 % RH, 40 °C

Standards and regulations

Standards/specifications	EN 60934
--------------------------	----------

Mounting

Mounting type	on base element
---------------	-----------------

TCP 10A - Thermal device circuit breaker


0712314

<https://www.phoenixcontact.com/us/products/0712314>



Drawings

Dimensional drawing




TCP 10A - Thermal device circuit breaker

0712314

<https://www.phoenixcontact.com/us/products/0712314>



Dimensional drawing



TCP 10A - Thermal device circuit breaker

0712314

<https://www.phoenixcontact.com/us/products/0712314>



Product drawing



The figure shows the product with the base element PT 6-FSI/C-LED 24 (Item No.: 3212172).


TCP 10A - Thermal device circuit breaker



0712314

<https://www.phoenixcontact.com/us/products/0712314>

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks


TCP 10A - Thermal device circuit breaker



0712314

<https://www.phoenixcontact.com/us/products/0712314>

Application drawing




Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

TCP 10A - Thermal device circuit breaker


0712314


<https://www.phoenixcontact.com/us/products/0712314>

Application drawing



Application drawing





Trigger characteristic

TCP 10A - Thermal device circuit breaker



0712314

<https://www.phoenixcontact.com/us/products/0712314>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0712314>

 CSA Approval ID: 074317				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	250 V	10 A	-	-

 cUL Recognized Approval ID: FILE E 140459

 UL Recognized Approval ID: FILE E 140459
--

 VDE Zeichengenehmigung Approval ID: 40034332
--

 CCC Approval ID: 2025010307749780

UAE-RoHS Approval ID: 23-10-88896

TCP 10A - Thermal device circuit breaker



0712314

<https://www.phoenixcontact.com/us/products/0712314>

Classifications

ECLASS

ECLASS-13.0	27140401
ECLASS-15.0	27140401

ETIM

ETIM 9.0	EC003538
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TCP 10A - Thermal device circuit breaker



0712314
<https://www.phoenixcontact.com/us/products/0712314>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	1.373 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com