

Ratings

Voltage: 600 V
Temperature: -40~105 °C
Flammability: FT2

Conductor

Conductor count: 6
Gauge: 24 AWG 0.21 mm²
Material: tinned copper strands
Strand size: $\phi 0.08 \times 41$
Resistance at 20 °C: 94.2 Ω /km max

Insulator

Material: mPPE
Color: red, black, white, yellow, blue, green
Diameter: $\phi 1.1 \pm 0.10$ mm
Average thickness: 0.24 mm
Resistance at 20 °C: 100 M Ω /km min

Filler

Material: cotton rope

Wrap

Material: cotton paper



Outer jacket

Material: mPPE, 85A
Color: black
Diameter: $\phi 5 \pm 0.20$ mm
Average thickness: 0.8 mm

Wire marking: E339579 UL AWM STYLE 21509 24 AWG 105°C
600V --- cUL AWM I A 105°C 600V FT2 TENSILITY

Bend radius

Minimum: 6 times diameter (30.0 mm)



Revision:	Date:	Description:	Prepared:	Notes:	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com		
A	5/5/2021	Initial release	Verified:	RoHS compliant Phthalate and halogen free			
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description: Wire, 6C TS, 24 AWG, 21509, 600V, 105C, 5.0 mm, FT2, mPPE	Size: A	Part number: 30-02009	Sheet 1 of 1
					Scale: 12:1		

5

4

3

2

1