



REV.	DATE	DESCRIPTION
A	01/25/04	UPDATE DRAWING FORMAT
B	12/31/05	MODIFY PART DESCRIPTION TO "COUPLING NUT"



RECOMMENDED
CABLE STRIPPING DIM'S



1. CONTACT PIN TO SOLDER

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
7						DRAWN	G.R.S.	12/31/05											
6	RETAINER RING	BER. COPPER	NATURAL	1		CHECKED									PART DESCRIPTION				
5	GASKET	SILICONE	RED	1							SMA DIRECT SOLDER PLUG (FOR .085", .086" CABLE)								
4	CONTACT PIN	BRASS	GOLD	1		ISSUED													
3	INSULATOR	TEFLON	NATURAL	1		SHEET	1 OF 1				PART NO.								
2	BODY	BRASS	GOLD	1							132188								
1	COUPLING NUT	STAINLESS STEEL	PASSIVATED S.S.	1															
DESCRIPTION		MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE	C:/132/132188.DWG		DWG. NO.		132188.DWG		REV.	B	SIZE	A	SCALE	NA