© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

HEAT SHRINK TUBING



✔ Active

TE CONNECTIVITY (TE)

LSTT-9.5-0-SP

Raychem | LSTT

LSTT-9.5-0-SP
TE Internal Number: 7798054001
Alias ID: 2-1196068-3

EU RoHS Compliant
EU ELV Compliant

Wall Type Single

Resistant To Mechanical Damage

Low Outgassing No

Product Source Czech Republic

Packaging Method Spool

DOCUMENTATION

Catalog Pages/Data Sheets

LSTT Pages From 9-1773447-9
PDF
English

At-Application-Tooling-For-Raychem-Heat-Shrink-Product-2-1773452-8
PDF
English

Product Specifications

Product Specification

LSTT Sleeving
PDF
English

Product Environmental Compliance

Downloaded from Arrow.com.

Safety Data Sheet

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Thermofit Heat-Shrinkable Polymeric Products

PDF

Danish

Thermofit Heat-Shrinkable Polymeric Products

PDF

Dutch

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Thermofit Heat-Shrinkable Polymeric Products

PDF

French

Thermofit Heat-Shrinkable Polymeric Products

PDF

German

Thermofit Heat-Shrinkable Polymeric Products

PDF

Italian

Thermofit Heat-Shrinkable Polymeric Products

PDF

Norwegian

Thermofit Heat-Shrinkable Polymeric Products

PDF

Spanish

Thermofit Heat-Shrinkable Polymeric Products

PDF

Swedish

Thermofit Heat-Shrinkable Polymeric Products

PDF

Spanish

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Thermofit Heat-Shrinkable Polymeric Products

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Global Dimensional Life For RAYCHEM Heat Shrink Tubing Standard Size Products (Customer Distribution)

PDF

English

Downloaded from Arrow.com.

FEATURES

Please review product documents or contact us for the latest agency approval information.

Product Type Features

Wall Type Single
Product Family LSTT

Electrical Characteristics

Voltage (Max) (kV) .6

Body Features

Shrink Ratio 2:1
Color Black
Flexibility Very Flexible
Material Irradiated Modified Polyolefin
Fluid Type Antifreeze, Battery Acid, Diesel Fuel, Gasoline, Hydraulic Fluid, Lubricating Oil, Water

Dimensions

Expanded Inside Diameter (Min) 9.5 mm [.374 in]
Recovered Wall Thickness (Nominal) .65 mm [.0255 in]
Recovered Inside Diameter (Max) 4.8 mm [.189 in]
Recovered Wall Thickness (Tolerance) .1 mm [.004 in]

Usage Conditions

Shrink Temperature (Min) (°C) 65
Resistant To Mechanical Damage
Recovery Temperature (°C) 110
Operating Temperature Range (°C) -40 – 125
Flammability Non-Flame-Retardant
Fluid Resistance Splash Protection

Product Availability

Applicable Region Global

Packaging Features

Packaging Method Spool

Other

Low Outgassing No
Product Source Czech Republic

PRODUCT COMPLIANCE

Statement of Compliance

Downloaded from Arrow.com.

Statement of Compliance

PDF

Downloaded from Arrow.com.