





插頭部件 (Plug Component)			頭部剝皮尺寸 (Dimensions)			線材規格 (Wire Stlys)	尾部剝皮尺寸 (Dimensions)			尾插部件 (Connector Component)		
顏色(Color)	零件描述(Component)	Qty.	內剝(Strip)	外剝(ROJ)	顏色(Color)	HO5VV-F 1.0mm ² x3C 70°C 黑色 (BLACK) Length : 1981.2±25.4 (78"±1")	外剝(R.O.J)	內剝(Strip)	顏色(Color)	規格描述(Instruction)	Qty.	顏色(Color)
45P 黑色 (Black)	SY-27 (CEE7 st. sh VII, Schuko, 16A 250V~)	1	8±1	35±2	棕/Brown(L)		18 ±2	5 ⁺¹ ₋₀	棕/Brown(L)	ME-307 (NEMA 5-15R)	1	35P 黑色 (Black)
黑色 (Black)	ø4.76 法國頭支架, GEM 98651 (VDE Plug Insert)	1	8±1	35±2	藍/Blue(N)		18 ±2	5 ⁺¹ ₋₀	藍/Blue(N)	ø4.75 D型母端 (GEM 98575-0) (D-Type Receptacle Terminal)	1	銅本色 (Brass-Natural)
			8±1	35±2	綠注黃 (E) Green-Yellow		18 ±2	5 ⁺¹ ₋₀	綠注黃 (E) Green-Yellow	尾插端子 (GEM 98752-0) (Receptacle Terminal)	2	銅本色 (Brass-Natural)
										022-2兩件式內模 (022-2 Inner Body)	1	黑色 (Black)




SY-27 (CEE7 st. sh VII, Schuko, 16A 250V~)
(Dimensions of Plug Face)



HO5VV-F 1.0mm²x3C截面圖
(Wire Cross-Section)



B-C2 扎線圖示 (Tied Loop Hank Detail)



ME-307 (NEMA 5-15R)
(Dimensions of Connector Face)

REV	DATE	REVISE CONTENT
A	03/07-2013	The first edition is issued and drawing.

NOTE:

- Hi-Pot Test : 2000V/1Sec ; <0.5mA.
- Insulation Resistance Test : DC 500/min>100 meg-ohm.
- Continuity & Polarization Test : No short circuit, break circuit, displacement.
- Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening.
- Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening.
- All material according to Non-toxic standard.(Material must be RoHS compliant.)

線材印字 (Wire Printed)		充實, 油墨印字 (Un-Fillers, Printing Ink)				CnC Tech, LLC			
包裝方式 (Packing)			DRAWN <i>Chu8.</i>			Industrial Cable and Connector Technology			
Tied Hank	See Hank Detail								
Carton Size	480 x 320 x 250		DATE 03/07-2013			CUSTOMER			
Pack Number	75 pcs					P/N No.	800-0.75-44L-BL-00200		
Carton Print	See Purchase Order								
TYPE	CEE7 st. sh VII, Schuko to NEMA 5-15R, 16A 250V~					MATERIAL	PVC	UNIT	mm
DRAWNING NO.	067MM099		REV	A	Customer Approval				