



Power Rectifiers Diodes (T-modules), 40 A to 110 A



D-55 (T-module)

FEATURES

- Electrically isolated base plate
- Types up to 1200 V_{RRM}
- 3500 V_{RMS} isolating voltage
- Simplified mechanical designs, rapid assembly
- High surge capability
- Large creepage distances
- UL E78996 approved 
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

I _{F(AV)}	40 A to 110 A
Type	Modules - diode, high voltage
V _{RRM}	100 V to 1200 V
Package	D-55 (T-module)
Circuit configuration	Single diode

DESCRIPTION / APPLICATIONS

These series of T-modules use standard recovery power rectifier diodes. The semiconductors are electrically isolated from the metal base, allowing common heatsink and compact assembly to be built.

Applications include power supplies, battery charges, welders, motor controls and general industrial current rectification.

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	T40HF	T70HF	T85HF	T110HF	UNITS
I _{F(AV)}		40	70	85	110	A
	T _C	85	85	85	85	°C
I _{F(RMS)}		63	110	134	173	A
I _{FSM}	50 Hz	570	1200	1700	2000	A
	60 Hz	600	1250	1800	2100	
I ² _t	50 Hz	1630	7100	14 500	20 500	A ² s
	60 Hz	1500	6450	13 500	18 600	
I ² √t		16 300	70 700	148 700	204 300	A ² √s
V _{RRM}		100 to 1200				V
T _J		-40 to +150				°C

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	V _{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V _{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I _{RRM} MAXIMUM AT T _J = 25 °C μA
VS-T40HF... VS-T70HF... VS-T85HF... VS-T110HF...	10	100	150	100
	20	200	300	
	40	400	500	
	60	600	700	
	80	800	900	
	100	1000	1100	
	120	1200	1300	



FORWARD CONDUCTION										
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES				UNITS	
					T40HF	T70HF	T85HF	T110HF		
Maximum average forward current at case temperature	I _{F(AV)}	180° conduction, half sine wave			40	70	85	110	A	
					85	85	85	85	°C	
Maximum RMS forward current	I _{F(RMS)}				63	110	134	173	A	
Maximum peak, one-cycle forward, non-repetitive surge current	I _{FSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T _J = T _J maximum	570	1200	1700	2000	A	
		t = 8.3 ms			600	1250	1800	2100		
		t = 10 ms	100 % V _{RRM} reapplied		480	1000	1450	1700		
		t = 8.3 ms			500	1050	1500	1780		
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		1630	7100	14 500	20 500	A ² s	
		t = 8.3 ms			1500	6450	13 500	18 600		
		t = 10 ms	100 % V _{RRM} reapplied		1150	5000	10 500	14 500		
		t = 8.3 ms			1050	4570	9600	13 200		
Maximum I ² √t for fusing	I ² √t	t = 0.1 ms to 10 ms, no voltage reapplied			16 300	70 700	148 700	204 300	A ² √s	
Low level value of threshold voltage	V _{F(TO)1}	(16.7 % × π × I _{F(AV)} < I < π × I _{F(AV)}), T _J maximum			0.66	0.76	0.68	0.68	V	
High level value of threshold voltage	V _{F(TO)2}	(I > π × I _{F(AV)}), T _J maximum			0.84	0.95	0.90	0.86		
Low level value of forward slope resistance	r _{f1}	(16.7 % × π × I _{F(AV)} < I < π × I _{F(AV)}), T _J maximum			4.3	2.4	1.76	1.56	mΩ	
High level value of forward slope resistance	r _{f2}	(I > π × I _{F(AV)}), T _J maximum			3.1	1.7	1.08	1.12		
Maximum forward voltage drop	V _{FM}	I _{FM} = π × I _{F(AV)} , T _J = 25 °C, t _p = 400 μs square pulse Average power = V _{F(TO)} × I _{F(AV)} + r _f × (I _{F(RMS)}) ²			1.30	1.35	1.27	1.35	V	

BLOCKING							
PARAMETER	SYMBOL	TEST CONDITIONS	T40HF	T70HF	T85HF	T110HF	UNITS
Maximum peak reverse leakage current	I_{RRM}	$T_J = 150^\circ\text{C}$	15	15	20	20	mA
RMS isolation voltage	V_{ISOL}	50 Hz, circuit to base, all terminals shorted $T_J = 25^\circ\text{C}$, t = 1 s	3500	3500	3500	3500	V

THERMAL AND MECHANICAL SPECIFICATIONS								
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES				UNITS
				T40HF	T70HF	T85HF	T110HF	
Maximum junction operating and storage temperature range	T _J , T _{Stg}			-40 to +150				°C
Maximum thermal resistance, junction to case per junction	R _{thJC}	DC operation		1.36	0.69	0.62	0.47	K/W
Maximum thermal resistance, case to heatsink	R _{thCS}	Mounting surface smooth, flat and greased		0.2				
Mounting torque, to heatsink ± 10 % terminals		Non-lubricated threads	M3.5 mounting screws ⁽¹⁾	1.3 ± 10 %				Nm
			M5 screw terminals	3 ± 10 %				
Approximate weight		See dimensions - link at the end of datasheet		54				g
Case style				D-55 (T-module)				

Note

⁽¹⁾ A mounting compound is recommended and the torque should be rechecked after a period of about 3 hours to allow for the spread of the compound



ΔR CONDUCTION PER JUNCTION

DEVICES	SINUSOIDAL CONDUCTION AT T _J MAXIMUM					RECTANGULAR CONDUCTION AT T _J MAXIMUM					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
T40HF...	0.12	0.14	0.18	0.27	0.46	0.09	0.15	0.20	0.28	0.46	K/W
T70HF...	0.09	0.11	0.14	0.20	0.35	0.07	0.11	0.15	0.21	0.35	
T85HF...	0.08	0.09	0.12	0.18	0.31	0.06	0.10	0.13	0.19	0.31	
T110HF...	0.05	0.07	0.09	0.14	0.23	0.05	0.08	0.10	0.15	0.24	

Note

- Table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 7 - Current Ratings Characteristics




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 8 - Current Ratings Characteristics




Fig. 9 - Forward Power Loss Characteristics




Fig. 10 - Forward Power Loss Characteristics




Fig. 11 - Maximum Non-Repetitive Surge Current




Fig. 12 - Maximum Non-Repetitive Surge Current




Fig. 13 - Current Ratings Characteristics




Fig. 14 - Current Ratings Characteristics




Fig. 15 - Forward Power Loss Characteristics




Fig. 16 - Forward Power Loss Characteristics




Fig. 17 - Maximum Non-Repetitive Surge Current




Fig. 19 - Current Ratings Characteristics




Fig. 18 - Maximum Non-Repetitive Surge Current




Fig. 20 - Current Ratings Characteristics




Fig. 21 - Forward Power Loss Characteristics




Fig. 22 - Forward Power Loss Characteristics




Fig. 23 - Maximum Non-Repetitive Surge Current




Fig. 25 - Forward Voltage Drop Characteristics




Fig. 24 - Maximum Non-Repetitive Surge Current




Fig. 26 - Forward Voltage Drop Characteristics




Fig. 27 - Forward Voltage Drop Characteristics




Fig. 28 - Forward Voltage Drop Characteristics




Fig. 29 - Thermal Impedance Z_{thJC} Characteristics

ORDERING INFORMATION TABLE

Device code	VS-	T	110	HF	120
	①	②	③	④	⑤
①	- Vishay Semiconductors product				
②	- Module type				
③	- Current rating				
④	- Circuit configuration (see Circuit Configuration table)				
⑤	- Voltage code x 10 = V_{RRM}				


CIRCUIT CONFIGURATION		
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Single diode	HF	

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95313



D-55 (T-Module) Diode Standard and Fast Recovery

DIMENSIONS in millimeters (inches)



Note

- 1 = Anode
- 2 = Cathode



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.