



marathon[®]
Special Products

Product Data Sheet

133X585

Replace "x" with 1, 2, or 3 for number of poles
Add suffix "CH" for snap-on hinged cover
Power Terminal Block

420 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 600 kcmil - #2 AWG
- Load: (8) #2 - 14 AWG

Electrical Ratings

- 420 Amps
- 600V per UL 1059 & CSA 22.2 No.158, Class B & C requirements
- Short circuit current ratings (SCCR): See SCCR section below for specifications.
- CU7AL - 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1


Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: aluminum, tin plated
- Line terminal screws: aluminum, tin plated
- Load terminal screws: steel, nickel plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

A Regal Brand

REGAL

Termination Specifications

Line Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	600 - 500 kcmil	42.4 N·m (375 lbf·in)	1	B, C
	400 - 2	42.4 N·m (375 lbf·in)	1	B, C, G, H, I (DLO)

- Aluminum stranded wire range: 600kcmil - #2 AWG
- Wire strip length: 1 9/16in. (40mm)
- Terminal screw drive: 1/2 in. hex

Load Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	2 AWG	6.8 N·m (60 lbf·in)	1	B, C
	4 - 6	6.8 N·m (60 lbf·in)	1	B, C, G, H, I (DLO)
	8	4 N·m (35 lbf·in)	1 - 2 ²	B, C, G, H, I (DLO)
	10	4 N·m (35 lbf·in)	1 - 2	B, C, I (DLO)
	12 - 14	4 N·m (35 lbf·in)	1 - 4	B, C
1 - 2			I (DLO)	

- Solid copper wire range: #10 - 14 AWG
- Aluminum stranded wire range: #2 - 8 AWG
- Wire strip length:
 - top row: 11/16 in. (17.5mm)
 - bottom row: 1 1/16. (27mm)

¹ For information on copper stranded wire classes please visit:
<http://www.marathonsp.com/flexible-stranded-wire.php>

² Multiple wire rating applies to class B, C, & I

Short Circuit Current Ratings (SCCR)

- The suitable conductor ranges are limited to the table values only for achieving the SCCR in excess of the default rating of 10,000A.
- Other conductor combinations within the “Terminal Specifications” noted are suitable for achieving a SCCR of 10,000A (the default rating of terminal blocks).
- Enclosure size – Investigated with a minimum 16x12x6 enclosure. Use in smaller enclosures is subject to end use evaluation.

SCCR With Fuses

Wire Class	Suitable Conductors		Max Overcurrent Protection Fuse Required Amp Rating / Class						SCCR RMS Sym. Amps 600V. Max
	Line	Load	J	T	RK1	RK5	G	CC	
B, C	600 - 3/0	2 - 8	400	400	400	200	60	30	100,000
B, C	600 - 2	2 - 10	200	200	200	100	60	30	100,000
G, H, I	350 - 2	4 - 10	150	150	100	30	60	30	100,000
(*)	600 - 2	2 - 14	None						10,000

* Any wire class evaluated (see terminal specification section)

Installation & Accessories

- Mounting (Panel):
 - For use with #10 fastener.
 - Mounting torque to be determined in end use application not to exceed 30 lbf-in (3.4 N-m).
- Covers:
 - Snap-on hinge covers available upon request
 - Catalog Number: CH133x (replace “x” with number of poles)
 - Covers are black thermoplastic
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

