


ROHS PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P91C*GL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P91C*GL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P91C*GL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P91C*GL00LF

Plating: 4 --> 200 Mating  
 Plating: 6 --> 500 Mating  
 Plating: 8 --> 1.25 $\mu$  Equivalent PdNi/Au

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:  
 SEE DRAWING C01-8646-0001

PC board drilling dimensions(after plating)



mat'l. code				surface	tolerance	projection	product family
ltr	ecn no	dr	date	ISO 1302	ISO 406 ISO 1101		D-SUB
L	ELX-I-21654	AB	2015-10-26	tolerances unless otherwise specified	.0±0.1	mm	
M	ELX-I-24020	AAB	2016-06-06	angles	.00±0.1	scale 2:1	
				linear	0±2°		
					.000±0.1		
		dr	JARRY	1994-09-21			
		engn	MITHUN PAUL	2016-06-06			
		chr	ATHUL A.B	2016-06-06			
		appd	BIJU K PAUL	2016-06-06			
sheet	revision	M					
index	sheet	1					