




Technical Data

22.03.2021

TREDUX MA47 - medium wall adhesive lined
Heat shrinkable tubing up to 4:1 - 1 m lengths

TREDUX-MA47-50/16

Article Number 323-50500



Material: Polyolefin, cross-linked (PO-X)
Colour: Black (BK)
Adhesive: Hot melt adhesive

Supplied Ø D min.: 50.0 mm
Recov. Ø d max.: 16.0 mm
Wall (WT): 2.7 mm
Shrink Ratio: up to 4:1
Longitudinal Change After Shrinkage: -10 % max.
Min. Shrink Temperature - °C: +120 °C

Test Method

Flammability: not flame retardant
Operating Temperature - °C: -55 °C to +110 °C
Heat Shock Test: 4h/225°C
Behaviour at Heat Shock: not cracking, not fluid, not dripping
Heat Aging Test: 168h/150°C
Minimum Tensile Strength At Heat Aging: 12 MPa
Elongation At Heat Aging: 300 %
Behaviour At Low Temperature: not cracking

ASTM D2671

ASTM D2671

Dielectric Strength: 15 kV/mm
Insulation Class: A (VDE 0530)
Tensile Strength: 12 MPa
Elongation at break: 350
Water Absorption: 0.2 %

IEC 60243

ASTM D2671

ASTM D2671



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved