




RoHS



bel

POWER | PROTECT | CONNECT

DOCUMENT / PART NO.: 0875-1G2T-E3

TITLE : PRODUCT SPECIFICATION

ISSUE	DESCRIPTION OF CHANGE					REVIEWED BY					APPROVED BY					ECN#
A	FIRST ISSUE					BILL CHEN					SHUN LEUNG 2006-10-14					
B	ADD PANENTED INFORMATION AND UPDATE ROHS DESCRIPTION & OTHER GENERAL REQUIREMENT					ANTON LIAO					LEUNG WAI SHUN 2012-08-31					RD2120187
C	UPDATE THE GENERAL REQUIREMENT					ANTON LIAO					LEUNG WAI SHUN 2018-01-19					RD2180011
D	CORRECT SOME PRODUCT VIEWS					LI QUAN KUN					LEUNG WAI SHUN 2021-03-16					RD2210022
E	MOVE THE LASER MARK OF P/N, DATE CODE AND PATENTED ON TOP SURFACE AND REMOVE BACK VIEW					TONY YUAN					 WaiShun Leung 2025.10.15 16:53:13 +08'00'					RD2250045
PAGE	1	2	3	4	5											
REV.	E	E	E	E	E											
PAGE																
REV.																

THE INFORMATION CONTAINED HEREIN IS CONSIDERED
"PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE
COPIED, REPRODUCED OR DISCLOSED WITHOUT THE
WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



LED2 POLARITY			LED1 POLARITY		
PIN 11	PIN 12	COLOR	PIN 13	PIN 14	COLOR
+	-	GREEN	+	-	GREEN

ELECTRICAL CHARACTERISTICS @ 25°C

URNS RATIO

TP1	1CT : 1CT $\pm 2\%$
TP2	1CT : 1CT $\pm 2\%$
TP3	1CT : 1CT $\pm 2\%$
TP4	1CT : 1CT $\pm 2\%$

OCL @ 100kHz/100mVRMS

8mA DC BIAS (0°C - 70°C)	350 μ H MIN.
--------------------------	------------------

INS. LOSS

100KHz TO 125MHz	-1.2 dB MAX
------------------	-------------

RET. LOSS (MIN) @ 100 Ω HMS $\pm 15\%$

0.5MHz-40MHz	-18 dB
40MHz-100MHz	-12+20LOG(f/80MHz) dB

CM TO CM REJ

100kHz - 100MHz	-30 dB MIN
-----------------	------------

CM TO DM REJ

100kHz - 100MHz	-35 dB MIN
-----------------	------------

CROSS TALK

1MHz-100MHz	-35 dB MIN
-------------	------------

HIPOT (Isolation Voltage):

1500 Vrms


100% OF PRODUCTION TESTED TO COMPLY WITH
IEEE 802.3 ISOLATION REQUIREMENTS.

LED 1 & 2


VF (FORWARD VOLTAGE)	IF=20mA GREEN 2.2V TYP.
λ D (DOMINANT WAVELENGTH)	IF=20mA GREEN 570nm TYP.

OPERATING TEMPERATURE

0°C TO +70°C






ORIGINATED BY BILL LIU DATE 2025-09-15		TITLE 1X2 gigabit MagJack® (WITH LED) PATENTED	PART NO. / DRAWING NO. 0875-1G2T-E3		STANDARD DIM. TOL. IN INCH		[] METRIC DIM. AS REF.		 bel MAGNETIC SOLUTIONS a bel group
DRAWN BY FRANK LIU DATE 2025-09-15			FILE NAME 0875-1G2T-E3_E.DWG		.X		UNIT : INCH [mm]		
					.XX		SCALE : N/A		
					.XXX			SIZE : A4	



bel MAGNETIC SOLUTIONS
a bel group

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



NOTES:

PLASTIC HOUSING: THERMOPLASTIC PBT, BLACK
FLAMMABILITY RATING UL 94V-0
CONTACTS PLATING: 30 MICRO-INCH HARD GOLD PLATING OR EQUIVALENT.
PINS: TIN-COATED COPPER WIRE, DIA 0.018 INCH.
100 MICRO-INCH MIN MATTE TIN.
PINS ARE SOLDER DIPPED.
METAL SHIELD: NICKEL PLATED ON COPPER ALLOY.
(ALL GROUND LEADS ARE SOLDER DIPPED)

1. MARK PART WITH MFG LOGO, MFG NAME, PART NUMBER, DATE CODE AND PATENTED.
2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS.
3. THE PRODUCT IS RoHS COMPLIANT.

cFUS UL RECOGNIZED - FILE #E196366 AND E169987.


4. THE PRODUCT IS PATENT PRODUCT, THE PATENT NUMBER IS U.S. PAT. 6,840,817.
5. THE PART IS RECOMMENDED FOR WAVE SOLDERING. THE SUGGESTED PEAK WAVE SOLDERING CONDITION IS 260°C MAX. AND 10 SECONDS MAX..

REV. : E		PAGE : 3	
ORIGINATED BY TONY YUAN DATE 2025-09-15	TITLE 1X2 gigabit MagJack® (WITH LED) PATENTED	PART NO. / DRAWING NO. 0875-1G2T-E3	STANDARD DIM. TOL. IN INCH
DRAWN BY JARRY YE DATE 2025-09-15		FILE NAME 0875-1G2T-E3_E.DWG	[] METRIC DIM. AS REF.
			UNIT : INCH [mm]
			SCALE : N/A
			SIZE : A4



THE INFORMATION CONTAINED HEREIN IS CONSIDERED
"PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE
COPIED, REPRODUCED OR DISCLOSED WITHOUT THE
WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



RECOMMENDED PCB FOOTPRINT
COMPONENT SIDE VIEW

ORIGINATED BY
TONY YUAN
DATE 2025-09-15

DRAWN BY
JARRY YE
DATE 2025-09-15

TITLE
1X2 gigabit MagJack®
(WITH LED)
PATENTED

PART NO. / DRAWING NO.
0875-1G2T-E3

FILE NAME
0875-1G2T-E3_E.DWG

STANDARD DIM.
TOL. IN INCH

.X
.XX
.XXX ±0.004

[] METRIC DIM.
AS REF.

UNIT : INCH [mm]
SCALE : N/A
SIZE : A4

REV. : E PAGE : 4




THE INFORMATION CONTAINED HEREIN IS CONSIDERED
"PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE
COPIED, REPRODUCED OR DISCLOSED WITHOUT THE
WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



SUGGESTED PANEL OPENING



NOTES:

THE DISTANCE OF PANEL INSIDE SURFACE RELATIVE TO FRONT SURFACE OF PART IS ONLY A SUGGESTION.
IN CASE THIS DISTANCE IS DIFFERENT, THE REQUIRED PANEL OPENING DIMENSIONS CHANGE ACCORDINGLY.

PACKING INFORMATION

PACKING TRAY : 0200-9999-G4 (TOP)

0200-9999-G5 (BOTTOM)

PACKING QUANTITY : 49 PCS FINISHED GOODS PER TRAY

8 TRAYS (392 PCS FINISHED GOODS) PER CARTON BOX

NOTE : CARDBOARDS ARE PLACED BETWEEN LAYERS OF PACKING TRAY INSIDE CARTON BOX
(INCLUDE THE UPPERMOST AND LOWERMOST TRAY)

REV. : E	PAGE : 5
	

ORIGINATED BY TONY YUAN DATE 2025-09-15	TITLE 1X2 gigabit MagJack® (WITH LED) PATENTED	PART NO. / DRAWING NO. 0875-1G2T-E3	STANDARD DIM. TOL. IN INCH	[] METRIC DIM. AS REF.
DRAWN BY JARRY YE DATE 2025-09-15		FILE NAME 0875-1G2T-E3_E.DWG	.X	UNIT : INCH [mm]
			.XX	SCALE : N/A
			.XXX ±0.005	SIZE : A4