






REV.	DATE	DESCRIPTION
NC	05/27/98	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT
B	02/05/08	ADD COUPLING NUT IN PART CALL OUT – ADD S/S MATERIAL



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .128"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8						DRAWN	G.R.S.	02/05/08							
7						CHECKED									
6	HEAT SHRINK TUBING			1		PART DESCRIPTION					SMA CRIMP PLUG, S/S COUPLING NUT (RG-174/U, 188A/U, 316/U)				
5	FERRULE	BRASS	NICKEL	1		ISSUED									
4	COUPLING NUT	S.S.	PASSIVATED S.S.	1		SHEET 1 OF 1									
3	CONTACT PIN	BRASS	GOLD	1							PART NO.				
2	INSULATOR	TEFLON	NATURAL	1							132174				
1	BODY	BRASS	NICKEL	1							DWG. NO. 132174.DWG				
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/132/132174.DWG					REV. B		SIZE A		SCALE NA