Ratings
Voltage: 300V
Temperature
Static: -40~105 °C
Dynamic: -20 to 105 °C
Flammability: VW-1
Water resistant: 75 °C
Oil resistant: 60 °C (jacket)
≥50% elongation and tensile strength after aging
UV resistance: jacket, 720 hours xenon or carbon arc exposure
≥80% tensile strength and elongation after aging

Conductor
Conductor count: 7
Gauge: 26 AWG 0.13 mm²
Material: tinned copper strands
Strand size: Ø 0.08 mm x 26
Resistance at 20 °C: 150 Ω /km Max


Insulator
Material: PVC
Color: red, black, white, yellow, blue, green, orange
Diameter: ∅1.3 ±0.10 mm
Nominal thickness: 0.38 mm
Resistance at 20 °C: 10 MΩ /km Min


Wrap
Material: cotton paper

Outer jacket
Material: PVC, 80A
Color: Black
Diameter: ∅5.6 ±0.25 mm
Nominal thickness: 0.8 mm

Wire marking: E339579 UL AWM STYLE 20387 26 AWG 105°C 300V VW-1 60°C OIL RESISTANT UV RESISTANT TENSILITY

Use: External wiring





Revision:	Date:	Description:
A	10/04/2021	Initial release

Prepared: MP Digitally signed by MP Date: 2021.10.21 09:40:46 -07'00'

Verified: AG Digitally signed by AG Date: 2021.10.22 14:01:27 -07'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:

RoHS compliant

Function test: no open, no short circuit, no intermittent

Description:
Wire, 7C TS, 26 AWG, UL20387, 300V, 105C, 60C oil, UV, 5.6 mm, VW-1, PVC, 80A, black

TENSILITY
tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com

Size: A
Part number: 30-01684
Scale: 10:1
Sheet 1 of 1

To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com

5 4 3 2 1

Downloaded from Arrow.com.