



Home> Products > Discrete Thermistors > 175 > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

175-503LAG-301



Surface mounted device 1206

Actual product appearance may vary.

Features

- Surface mountable for automated pick and place
- Glass-coated ceramic for long term reliability
- Solder plated nickel
- Versatile
- Solderable leads
- Available on tape and reel

Potential Applications

- Consumer electronics
- PCB temperature sensing
- Communications
- Computers
- Rechargeable battery packs
- Low -cost applications with a maximum temperature of 150 °C [302 °F]
- Automotive

Description

173 Series and 175 Series Thermistors are designed to be mounted using robotics onto rigid or flexible PC boards. They are particularly suited for PC boards with a high density of discrete components. The solder-plated, nickel barrier terminations are easily soldered and meet ANSI/JSTD-002 Method B. These products are designed to withstand solder temperatures of 260 °C for 30 seconds. Available on tape and reel for automated assembly.

Supporting Documentation

None Available

Product Specifications	
Availability	Global
Nominal Resistance at 25 °C [77 °F]	50,000 Ohm
Tolerance	± 10.0%
Accuracy	25 °C [77 °F]
R- T Curve	16
Operating Temperature Range	- 60 °C to 125 °C [- 76 °F to 257 °F]
Maximum Diameter	EIA 1206 SMD
Time Constant in Air	10.0 s
Dissipation Constant	3,5 m/W°C
Series Name	175

My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

Product Search

Part number search:

Use (*) to expand search

Specification Search