





PRODUCT NUMBER

PITCH

V8xx31x000J0G

3.81 mm



Material:

- Item ③ Insulator (Body): Thermoplastic (UL94V-0)
- Item ④ Insulator (Cover): Thermoplastic (UL94V-0)
- Item ⑤ Terminal screw: Steel Zinc plating "-" slot type
- Item ⑥ Terminal body: Brass (CuZn) Ni plating
- Item ⑦ Pin: Brass, Tin plated

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 8A
- Solid wire (AWG): 14-30
- Stranded wire (AWG): 14-30
- Torque (Lb-In): 2.6
- Screw: M2
- Wire strip length: 7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

Dimension

Dim A	N×3.81
Dim B	N×3.81+0.88
Dim C	(N-1)×3.81

N=Number of poles

POLES	Tolerance
2p-6p	±0.15
7p-13p	±0.20
14p-18p	±0.30
19p-24p	±0.40

PART NO.: V8 xx 31 x 0 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
0	2	Black (RAL9005)	
1	3	Red (RAL3001/D)	
2	4	Orange (RAL2011/P)	
3	5	Yellow (RAL1018/A)	
4	6	Green (RAL6018/T)	
5	7	Blue (RAL5015/A)	
6	8	Grey (RAL7035/D)	
7	9	White (RAL1102)	
8	24	Green (RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family	
ltr ecn no dr date				ASME Y14.5 ✓	ASME Y14.5		TERMINAL BLOCK	
				tolerances unless otherwise specified		MM	title	
				angles	X.±0.5		TERMINAL BLOCK	
				holes	X.X±0.3		PLUGGABLE PLUG	
				X*±1°	X.XX±0.1	scale		
dr				EVIN ZHONG	050514		dwg no	
enr				EVIN ZHONG	050514		sheet 1 of 1	
chr				HANKE FENG	050514		V8xx31x000J0G	
appd				SHI JUN	050514		size	
sheet index				revision	A	type		CUSTOMER Drawing
sheet				1				