

8600 Series Rocker Switches

10A 250Vac Single & Double Pole




Ratings Information

10(4)A 250Vac T90 (unless noted below)
UL CSA 10A 277Vac (unless noted below)
UL CSA 277Vac ½ hp, 125Vac ¼ hp
UL 65°C, file no. E45221
CSA file LR10990

Inrush 25A to EN61058-1 & 10A 28Vdc (In house tests)
 3mm contact gap except where marked µ.

Order Format



Dimensions (All dimensions in mm)

Single Pole

Double Pole Standard is code 'B' with terminal barrier. (Also available without terminal barrier - specify code 'C')

Examples





H8600VB
T8600VB



H8600VB
T8600VB



H8630FB



T8630FB



H8650VB
T8650VB

Legend Printing Examples () is legend color B-Black, W-White, R-Red



577(W)



080(W)



141(W)



142(W)



059(W)








058(W)



H8660VB
T8660VB



H8653VB
T8653VB

TERMINAL CODE	SWITCH FUNCTION CODE		ROCKER CODE	BODY CODE		OPTIONS
H 	On Off Switches are ON when pressed over terminal 3		V Curved 	Panel cut-outs Flange		Finish Matt finish is standard Color Consult factory for custom colors. A full range is available for large orders Legend printing Select from the examples or call factory for custom legends Lamp voltage Consult factory for details of other available voltages Single pole options Most switches shown can have single pole switching in double pole bodies Moisture resistant covers (IP65) Will snap on to Single or Double Pole bodies but reduce panel thickness by 0.8mm Ask for (L167 - SP) or (L180 - DP) 
	Approvals & ratings vary with function			B (Single Pole)		
T 			V Curved Lit 	Single Pole dimensions for snap-in fixing		
				Panel thickness Dimension X		
				0.75 - 1.25 19.1 / 19.2		
				1.25 - 2.0 19.3 / 19.4		
X 			D Paddle lever Single pole non-lit only 	B (Double Pole) with terminal barrier		
				C (Double Pole) w/o terminal barrier		
						
				Double Pole dimensions for snap-in fixing		
		Panel thickness Dimension X				
		0.75 - 1.25 19.1 / 19.2				
		1.25 - 2.0 19.3 / 19.4				
		2.0 - 3.0 19.7 / 19.8				
		F Flat Indicator only (Single pole) 				

Technical Information

Most major technical information is shown on the page covering the specific product, other details are grouped here for easy reference.

The details shown apply to all Switches and Fuseholders. For electrical products, Indicators or IEC sockets see the individual product page.

Materials

Body and actuator (opaque)

Actuator (transparent)

Current carrying parts

Contact points

Most Products Expections

Nylon 6.6

Polycarbonate

Copper Alloy

Silver Plated

Silver Alloy

900 & 380 Vandal options are stainless steel

n/a for 55/56 & 2000, Gold plated for 1100

Properties - Electrical

Electrical Life (operations)

Contact Resistance (switches) new condition

(m ohms)

Contact Resistance (fuseholders) new condition

(m ohms)

Insulation Resistance (M ohms)

Dielectric Strength: (kV)

across open contacts

between poles

between live parts and accessible metal

Comparative Tracking Index (CTI)

>10k, many >50k See relevant page for details

<100 (at 12Vdc, 1100, 2000 contact factory

1A)

5 (average)

>20

>1

>3

>4

>250

Properties - Physical

Humidity Resistance at 91-95% relative humidity

(to subsequently comply with requirements of dielectric strength test)(hrs)

Impact Resistance (Nm)

Storage term 5 year period (°C)

Flame Retardancy:

Standard

On Request

Solderability to BS 2011 pt.2.1T -

Angular movement $\pm 4^\circ$ overall (where applicable)

Force to operate (Kg). For details contact Sales office

Fixing nut torque (where applicable)

48

>0.5

<125

Some discoloration of terminals may occur

UL94V2

UL94V0

6 secs at 350°C

38°

Polycarbonate actuators - UL94V2 only

Not all colors or variants

1250, 6000, 8500, 8550, 8600, 8650, 8800 - 26°

0.2 - 2.0

1.0Nm (8.91 lb/in)

General Information

All switches

Insulation Class II.

Heat and Fire resistance Category D.

Ingress Protection without cover IP40.

DC ratings are not approved.

All products

Panel holes must be punched in direction unit is to be fitted

Illuminated rockers and indicator lights

Transparent lenses on indicator lights and illuminated switches are moulded in polycarbonate, a material which is attacked by organic chemicals and animal or vegetable fats.

Please contact the factory for advice on these products.

Weights of our most frequently supplied products

Product	gms	Product	gms	Product	gms
0055,0056	5.7/6.8	1350	11.2	5567	14.3
0305	32.9	1500	5.7	6050	13.6
0333	4.5	1520	6.6	6053	14.2
0345	8.9	1550	11.2	7000	10.4
0380 sw only	7.12	1553	11.8	7050	12.3
0383K/P	25.0	1570	12.7	7053	12.9
0392	10.7	1584-1589	11.1	8250	4.9
0430	5.5	1700H	8.4	8300	4.0
0589	3.5	1750H	13.2	8350	5.0
0692	51.8	1750O	25.6	8353	5.9
0711-1S	16.6	2000 2pos C SP	3.8	8500	3.8
0712-S	27.8	2000 2pos C DP	4.5	8550	4.8
0717-1S	22.4	2000 5pos A SP	6.3	8553	5.2
0900S/L	2.6/2.9	2000 5pos A DP	7.3	8600	3.5
1048	2.8	T2225B	5.0	8620	4.3
1100	2.0	2950	5.3	8650	6.3
1250SP	5.9	3111	11.8	8670	8.5
1250DP	7.0	5500	7.1	8800	2.9
1300	5.7	5503	7.8	9100	21.1