


OGA DIAGONAL: 16.36 [415.52]
VA DIAGONAL: 15.65 [397.41]
PA DIAGONAL: 14.55 [369.64]

TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9621-203	98-0003-3169-8	FFC	4.27" [108.46]	AG500	23655
17-9621-205	98-0003-2969-2	FFC	8.00" [203.20]	AG500	23655
17-9621-226	98-0003-2970-0	USB R	8.00" [203.20]	AG500	23655
17-9621-227	98-0003-2972-6	SER	8.00" [203.20]	AG500	23655
17-9621-221	98-0003-3313-2	SER	4.27" [108.46]	AG500	23655
N/A	98-0003-3448-6	FFC	6.00" [152.40]	AG500	23655
N/A	98-0003-3458-5	USB R	6.00" [152.40]	AG500	23655
N/A	98-0003-3459-3	SER	6.00" [152.40]	AG500	23655
N/A	98-0003-4228-1	USB R	8.00" [203.20]	WC100	34523
N/A	98-0003-4230-7	SER	8.00" [203.20]	WC100	34523
N/A	98-1100-0091-0	FFC	8.00" [203.20]	WC100	34523



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 622±10%
2. NICOMATIC HOUSING P/N: OLO5
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	UL
2	UR
3	SHLD
4	LR
5	LL

UNITS INCHES [MM]		3M TOUCH SYSTEMS METHUEN, MA USA		REV		CHANGE NOTICE		DATE		DWG	
TOLERANCES UNLESS OTHERWISE SPECIFIED				TITLE MARKETING DRAWING SCT32NN 15.65" W							
.X ± .XX ±.03 [.76] .XXX ±.015 [.38] ANGLES ±1°		©COPYRIGHT 2004 THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE 3M COMPANY AND MAY NOT BE REPRODUCED WITHOUT 3M WRITTEN PERMISSION OR USED OR DISCLOSED FOR OTHER THAN 3M AUTHORIZED PURPOSES.									
THIRD ANGLE PROJECTION				DRAWN S.Berard 10/09/08		CAD FORMAT AUTOCAD		SHEET 1 OF 1			
DO NOT SCALE DRAWING				SIZE C		DOCUMENT NO. TSD-36245		REV K			
SCALE 1 = 1											