

# 10A, 60V Dual Common Cathode Trench Schottky Rectifier



## FEATURES

- Patented Trench Schottky technology
- Excellent high temperature stability
- Low power loss, high efficiency
- High forward surge capability
- Compliant RoHS
- Halogen-free according to IEC 61249-2-21

## APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application
- On-board DC/DC converter

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
$I_F$	2 x 5	A
$V_{RRM}$	60	V
$I_{FSM}$	90	A
$T_J \text{ MAX}$	150	°C
Package	TO-220AB	
Configuration	Dual dies	


**TO-220AB**


ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	TST10H60C	UNIT
Marking code on the device		TST10H60C	
Repetitive peak reverse voltage	$V_{RRM}$	60	V
Reverse voltage, total rms value	$V_{R(\text{RMS})}$	42	V
Forward current	per device	$I_F$	A
	per diode		A
Surge peak forward current single half sine-wave superimposed on rated load per diode	$t = 8.3\text{ms}$	$I_{FSM}$	A
	$t = 1.0\text{ms}$		A
Junction temperature	$T_J$	-55 to +150	°C
Storage temperature	$T_{STG}$	-55 to +150	°C

**THERMAL PERFORMANCE**

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance per diode	$R_{\Theta JL}$	3.8	°C/W
Junction-to-ambient thermal resistance per diode	$R_{\Theta JA}$	12.3	°C/W
Junction-to-case thermal resistance per diode	$R_{\Theta JC}$	3.6	°C/W

**Thermal Performance Note:** Mounted on Heat sink with 2" x 3" x 0.25" Al-Plate.

**ELECTRICAL SPECIFICATIONS** ( $T_A = 25^\circ\text{C}$  unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode <sup>(1)</sup>	$I_F = 2.5\text{A}, T_J = 25^\circ\text{C}$	$V_F$	0.46	-	V
	$I_F = 5.0\text{A}, T_J = 25^\circ\text{C}$		0.54	0.62	V
	$I_F = 2.5\text{A}, T_J = 125^\circ\text{C}$		0.36	-	V
	$I_F = 5.0\text{A}, T_J = 125^\circ\text{C}$		0.47	0.58	V
Reverse current @ rated $V_R$ per diode <sup>(2)</sup>	$T_J = 25^\circ\text{C}$	$I_R$	-	15	$\mu\text{A}$
	$T_J = 125^\circ\text{C}$		-	15	mA
Junction capacitance per diode	1MHz, $V_R = 4.0\text{V}$	$C_J$	375	-	pF

**Notes:**

1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms


**ORDERING INFORMATION**

ORDERING CODE	PACKAGE	PACKING
TST10H60C	TO-220AB	50 / Tube


## CHARACTERISTICS CURVES

( $T_A = 25^\circ\text{C}$  unless otherwise noted)


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Junction Capacitance**




**Fig.3 Typical Reverse Characteristics**




**Fig.4 Typical Forward Characteristics**



**Fig.5 Typical Transient Thermal Impedance**



**PACKAGE OUTLINE DIMENSIONS**
**TO-220AB**


DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.42	4.76	0.174	0.187
A2	2.20	2.80	0.087	0.110
b	0.68	0.94	0.027	0.037
b2	1.14	1.77	0.045	0.070
c	0.35	0.64	0.014	0.025
c2	1.14	1.40	0.045	0.055
D	14.60	16.00	0.575	0.630
D1	2.62	3.44	0.103	0.135
D2	5.84	6.86	0.230	0.270
E	-	10.50	-	0.413
e	2.41	2.67	0.095	0.105
L	13.19	14.79	0.519	0.582
L4	2.80	4.20	0.110	0.165
P	3.54	4.00	0.139	0.157

**MARKING DIAGRAM**


P/N = Marking Code  
 G = Green Compound  
 YWW = Date Code  
 F = Factory Code

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.