

### Features:

- High stability tantalum nitride film
- Available in 0402, 0603, 0805 and 1206
- TCR to  $\pm 10\text{ppm}/^\circ\text{C}$
- Sulfur resistant to ASTM B809-95
- Both Pb-free and SnPb finish available
- AEC-Q200 qualified



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)


### Electrical Data

		PFC0402	PFC0603	PFC0805	PFC1206
Power rating (@70°C)	mW	50	100	250	333
Rated operating voltage (not to exceed $\sqrt{P \times R}$ )	V	75		100	200
Resistance range	ohms	40R to 35K	40R to 100K	10R to 267K	10R to 1M0
Tolerance	%	0.05, 0.1, 0.25, 0.5, 1, 2, 5			
TCR	ppm/°C	10, 15, 25, 50, 100			
ESD withstand <sup>1</sup> (HBM)	kV	0.5	1	1.5	2
Noise	dB	<-25			
Operating temperature	°C	-65 to 150			
Values		E24 or E192			

Note 1: This product is not considered ESD sensitive for packaging and handling purposes.

### Physical Data

Dimensions in inches / (mm) and weight in mg						
Size	L	W	H	a	b	Wt. nom.
0402	0.04 $\pm$ 0.003 (1.02 $\pm$ 0.08)	0.021 $\pm$ 0.005 (0.53 $\pm$ 0.13)	0.012 $\pm$ 0.003 (0.3 $\pm$ 0.08)	0.01 $\pm$ 0.006 (0.25 $\pm$ 0.15)		0.55
0603	0.063 $\pm$ 0.004 (1.6 $\pm$ 0.1)	0.031 $\pm$ 0.004 (0.79 $\pm$ 0.1)	0.02 $\pm$ 0.006 (0.51 $\pm$ 0.15)	0.012 $\pm$ 0.008 (0.3 $\pm$ 0.2)	0.015 $\pm$ 0.009 (0.38 $\pm$ 0.23)	1.97
0805	0.081 $\pm$ 0.006 (2.06 $\pm$ 0.15)	0.05 $\pm$ 0.007 (1.27 $\pm$ 0.18)		0.015 $\pm$ 0.009 (0.38 $\pm$ 0.23)	0.016 $\pm$ 0.008 (0.41 $\pm$ 0.2)	4.48
1206	0.126 $\pm$ 0.008 (3.2 $\pm$ 0.2)	0.063 $\pm$ 0.005 (1.6 $\pm$ 0.13)	0.024 $\pm$ 0.006 (0.61 $\pm$ 0.15)	0.025 $\pm$ 0.017 (0.64 $\pm$ 0.43)		8.93



Note: For PCB mounting pad recommendations see:

<https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Application-Note/TN006-Recommended-Layouts-for-SMD-Resistors.pdf>


### Construction

Conductors and tantalum nitride resistive element are applied to an alumina substrate. The product is laser trimmed to value, and a protective epoxy coat is applied. The product is then metallized and plated to provide a wrap-around solderable termination with a 100% matte tin or a 60/40 SnPb finish on a nickel barrier layer. It is 100% tested then packed in carrier tape. Pb-free parts use paper carrier tape, whilst SnPb parts use plastic carrier tape.

Performance Data

Test per MIL-PRF-55342	±ΔR/R%	
	Typical	Maximum
Thermal shock	0.02	0.1
Low temperature operation	0.01	0.05
Short-time overload	0.01	0.05
High temperature exposure	0.03	0.1
Effects of solder	0.01	0.1
Moisture resistance	0.03	0.1
Life	0.03	0.1
Sulfuration test: ASTM B809 (modified) 105°C, dry, 1000 hours	0.02	0.05

Temperature Derating



Ordering Procedure

Global Part Number Example: PFC0402LFD1002BT5 (0402, 25ppm/°C at 10 kilohms ±0.1%, Pb-free)

P	F	C	0	4	0	2	L	F	D	1	0	0	2	B	T	5	
1			2		3	4			5		6		7				

1	2	3	4	5	6	7		
Series	Size	Termination <sup>1</sup>	TCR (ppm/°C)	Value	Tolerance	Packing		
PFC	0402	LF = Pb-free (100%Sn)	T = ±10	3 digits + multiplier R = ohms for values <100 ohms	A = ±0.05%	Pb-free (LF) product		
	0603	PB = SnPb (60/40)	Y = ±15		B = ±0.1%	T10	0402	10,000/reel
	0805	(0603, 0805, 1206 only)	D = ±25	C = ±0.25%	T5	0603, 0805, 1206	5000/reel	
	1206		C = ±50	D = ±0.5%	T1	All sizes <sup>2</sup>	1000/reel	
				Z = ±100	F = ±1%	SnPb (PB) product		
					G = ±2%	T1	0603, 0805, 1206	1000/reel
				J = ±5%				

Note 1: Terminations are anti-sulfur as standard.  
Note 2: Non-standard packing option – consult factory for availability.

### Legacy Part Numbers

This product has two legacy part number formats. These are still available for ordering, but for new designs use of the Global Part Number is recommended.

**European Legacy Part Number: W1206R-01-1K0B1** (1206, 100ppm/°C, 1 kilohm  $\pm 0.1\%$ , Pb-free)

W	1	2	0	6	R		-	0	1	-	1	K	0		B	1	
1	2	3	4	5	6	7											

1	2	3	4	5	6	7
Series	Size	Option <sup>1</sup>	TCR (ppm/°C)	Value	Tolerance	Termination & Packing
W = PFC	0402	R	-12 = $\pm 10$	E24/E96 =	A = $\pm 0.05\%$	I All sizes Pb-free, Standard pack
	0603	AS	-11 = $\pm 15$	3/4 characters	B = $\pm 0.1\%$	PB 0603, 0805, 1206 SnPb finish, 1000/reel
	0805		Blank = $\pm 25$	R = ohms	C = $\pm 0.25\%$	Standard Pack
	1206		-02 = $\pm 50$	K = kilohms	D = $\pm 0.5\%$	0402 10,000/reel
			-01 = $\pm 100$	M = megohms	F = $\pm 1\%$	0603, 0805, 1206 5000/reel
					G = $\pm 2\%$	
					J = $\pm 5\%$	

Note 1: Terminations are anti-sulfur as standard.

**USA Legacy Part Number: PFC-W1206LF-01-1001-B** (1206, 100ppm/°C, 1 kilohm  $\pm 0.1\%$ , Pb-free)

P	F	C	-	W	1	2	0	6	L	F		-	0	1	-	1	0	0	1	-	B
1	2	3	4	5	6																

1	2	3	4	5	6	Standard Packing
Series	Model	Termination <sup>1</sup>	TCR (ppm/°C)	Value	Tolerance	
PFC	W0402	LF	12 = $\pm 10$	3 digits + multiplier	A = $\pm 0.05\%$	0402 10,000/reel
	W0603	ASLF	11 = $\pm 15$		B = $\pm 0.1\%$	0603, 0805, Pb-free 5000/reel
	W0805	R	03 = $\pm 25$	R = ohms	C = $\pm 0.25\%$	1206 SnPb 1000/reel
	W1206	AS	02 = $\pm 50$	for values	D = $\pm 0.5\%$	
			01 = $\pm 100$	<100 ohms	F = $\pm 1\%$	
					G = $\pm 2\%$	
					J = $\pm 5\%$	

Note 1: Terminations are anti-sulfur as standard.