


Product description	M12 Male angled connector, Contacts: 8, 6.0-8.0 mm, shieldable, screw clamp, IP67, UL 2238, with shielding ring
Area	M12-A
Coding	A-coded
Series	713
Part no.	99 1487 822 08


Illustration (may vary)



Scale drawing



Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

Technical data

General features

Part no.	99 1487 822 08
Connector design	Male angled connector
Type standard	DIN EN 61076-2-101
Coding	A-coded
Version	Connector pin angled
Connector locking system	screw
Termination	screw clamp
Degree of protection	IP67
Connection cross-section	max. 0.25 mm ² / AWG 24
Cable outlet	6.0-8.0 mm
Twistability	not rotatable
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 500 Mating cycles
Weight (g)	63.79
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	30 V
---------------	------

Product data sheet

Automation technology - Sensors and actuators



Product description	M12 Male angled connector, Contacts: 8, 6.0-8.0 mm, shieldable, screw clamp, IP67, UL 2238, with shielding ring
Area	M12-A
Coding	A-coded
Series	713
Part no.	99 1487 822 08

Rated impulse voltage	800 V
Rated current	2.0 A
Insulation resistance	$> 10^8 \Omega$
Pollution degree	3
Overvoltage category	II
Insulating material group	III
EMC compliance	shieldable
Shield connection	Shielding ring

Material

Housing material	Zinc die-cast nickel-plated
Contact body material	PBT (UL94 V-0)
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	Zinc die-cast nickel-plated
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	9cb72ba6-b1cc-4bd8-87f5-cac638cd3310

Authorization/approvals

Approvals	UL 2238
-----------	---------

Classifications

eCl@ss 11.1	27-44-01-02
ETIM 9.0	EC002635


Trade-Compliance

Copper (9903.78.01)	0.000221 kg
---------------------	-------------

Product description	M12 Male angled connector, Contacts: 8, 6.0-8.0 mm, shieldable, screw clamp, IP67, UL 2238, with shielding ring
Area	M12-A
Coding	A-coded
Series	713
Part no.	99 1487 822 08

Assembly instructions

1. Bead pressing screw, pinch ring, seal and shielding ring to cable.
2. Dismantle cable.
3. Strip single wires, shorten shield and revert to shielding ring.
4. Thread single wires through angled housing, mount shielding ring, seal and pinch ring. Slightly tighten pressing screw to fix the cable.
5. Screw on single wires: 8 pole: 0.2 Nm.
6. Screw angled housing to male/female insert.
7. Fit seal to cover and insert cover.
8. Tighten pressing screw.



Product description	M12 Male angled connector, Contacts: 8, 6.0-8.0 mm, shieldable, screw clamp, IP67, UL 2238, with shielding ring
Area	M12-A
Coding	A-coded
Series	713
Part no.	99 1487 822 08

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).