


HONEYWELL PART NUMBER
122SM44-T2
PRODUCT CODE TYQ4480

REV	DOCUMENT	CHANGED BY	CHECK
8	0038225	PRS 04APR08	BLR



- NOTES
- 1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.	PR - 1352
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	VK	30 OCT 07		Honeywell			
OPERATING FORCE — — — — 7 OZ MAX		CONTACT ARRANGEMENT SPDT						CHECK	RJ	30 OCT 07					
RELEASE FORCE— — — — — 2 OZ MIN		30 VOLTS DC RATING			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC							
PRETRAVEL - - - - - .219 MAX			SEA LEVEL	50,000 FT											
DIFFERENTIAL TRAVEL— — — .025 MAX		INDUCTIVE	1/2 AMP	1/2 AMP											
OVERTRAVEL — — — — — .030 MIN		RESISTIVE	1 AMP	1 AMP											
		MAXIMUM INRUSH 2 AMP			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV			
		APPROVALS	KEMA, CE	1A, 250V ~ T85 1E4					CE	B	I	122SM44-T2		8	
			UL, CSA	1A, 125 VAC ~					CE	L 22	SCALE	-	WEIGHT .008 LB MAX	SHEET 1 OF 1	