

Product Status	Production
Applications	Commercial Grade
Feature	Multilayer Non-Mag Core Non-Magnetic Core (Dielectric Ceramic) Super High Q
Series   Type	MHQ-P
Brand	TDK
Environmental Compliance	 RoHS  REACH  Halogen Free  Lead Free



Size	
Length(L)	0.65mm ±0.05mm
Width(W)	0.35mm ±0.05mm
Thickness   Height	0.35mm ±0.05mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

Electrical Characteristics	
Inductance	24nH ±3% at 500MHz
Rated Current	160mA
DC Resistance [Typ.]	1.55Ω
DC Resistance [Max.]	2.2Ω
Self Resonant Frequency [Min.]	2.1GHz
Self Resonant Frequency [Typ.]	3.1GHz
Q [Min.]	16 at 500MHz
Q [Typ.]	





Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g

! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)




! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.