



RoHS Compliant




N=NUMBER OF POLES

Dim L	N×5.0+1.00
Dim B	(N-1)×5.0

POLES	Dim L
1p	±0.1
2p-6p	±0.2
7p-12p	±0.3
13p-18p	±0.4
19p-24p	±0.45



1 Pole



P.C.B. LAYOUT

Top view

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
D	△	01/24/07	The Soldering temperature from 245° to 250°	Aaron
	△	01/24/07	Add "VDE" stipulation	Aaron
E	△	05/19/09	wire strip length changed from 6-7mm to 9-10mm	Eris
	△	05/19/09	temperature changed from -30°C-105°C to -40°C-115°C	Eris
	△	05/19/09	The tolerance of dimension is changed	Eris
F	△	01/11/11	The view is changed	Runner
G	△	01/02/13	change the electrical specification and the dimension from 3.6 to 3.3	Da cheng
	△	11/11/19	Add the RoHS Compliant&Amphenol Logo.	Guoxue
	△	11/11/19	Update the VDE Current rating & Wire range	Guoxue
	△	11/11/19	Add the "Reference dimension"	Guoxue
	△	11/11/19	Update the VIEW.& Add the CQC.	Guoxue
	△	11/11/19	Add the "Wave Soldering temperature: 260°C±5°C/5 Sec	Guoxue
	△	11/11/19	Delete the Dim.B	Guoxue
	△	11/11/19	Add the 1 Pole VIEW	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- Material
- Item ① Terminal housing: Thermoplastic (UL94V-0)
 - Item ② Solder Pin: Brass Tin plated.
 - Item ③ Lever: Thermoplastic (UL94V-0) White color
 - Item ④ Spring clamp: Stainless steel
 - Item ⑤ Terminal Cover: Thermoplastic (UL94V-0)

Electrica	cULus	VDE	CQC
● Voltage rating:	300VAC	450VAC	450VAC
● Current rating:	10A	9A	24A
● Wire range:		0.2-0.75mm ²	0.5-2.5mm ²
● Solid wire(AWG):	14-20		
● Stranded wire(AWG):	14-20		
● Wire strip length:	9-10mm		
● Withstanding Voltage:	1.6KV	2.5KV	2.5KV
● Operating temperature:	-40°C to +115°C		
● Wave Soldering temperature:	260°C±5°C/5 Sec		

● Safety Approval:

● Critical dimension: (x) The dimensions of pitch are just for reference, take the actual assembly result as a judgment when inserting the terminal block into the PCB hole.

HBxx01x0xxxxG

- No. OF POLES
- 01: 1 POLES
- 02: 2 POLES
- ...
- 24: 24 POLES
- Body Color
- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange (RAL2011/P)
- 4 Yellow (RAL1018/A)
- 5 Green (RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey (RAL7004/P)
- 9 White (RAL1102)
- C Multiple colors
- 0000 Standard @ Logo
- 000A Standard ANY Logo
- Any special item by customer request, please contact sales department.
- RoHS compliant (lead<4%) In copper Alloy

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HB - 5.0mm Series (Single wire)						
PART NO.	HBxx01x0xxxxG			DWG NO.	8HB0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Guoxue 2019.11.11	Guoxue 2019.11.11		UNIT: mm	Tolerance	
					SCALE: NONE	X. ±0.50	
						X.X ±0.30	
						X.XX ±0.10	
						X° ±1°	

SHEET: 01/01

REV.: H