

Part Number : 638233600

Product Description : Hand Crimp Tool for ISO (M3)

Blade Terminals

Series Number : 207129

Status : Active

Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[ATS-6382336HM-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per ED/61/2018 (27 June 2018)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for ISO (M3) Blade Terminals
Comments	See Tooling Specification (PDF) Above; Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	884982769830
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

Mates With / Use With

Use with Part(s)

Description	Part Number
Modular Crimp Head for Hand Crimp Tool for MX150 ISO (M3) Blade Terminals	<u>638233670</u>

Applicable Parts

Description	Part Number
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Tin Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm ² , Right Reel Payoff	<u>330000004</u>
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Tin Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm ² , Left Reel Payoff	<u>330001004</u>
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Gold Plating, Grip Code M3, Left Reel Payoff, Contact Material Thickness 0.30mm, Preferred Terminal for use in Sealed Application with 0.35-0.50mm ²	<u>330110008</u>
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Gold Plating, Grip Code M3, Right Reel Payoff, Contact Material Thickness 0.30mm, Preferred Terminal for use in Sealed Application with 0.35-0.50mm ²	<u>330111008</u>
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Silver Plating, Grip Code M3, Right Reel Payoff, Contact Material Thickness 0.30mm, Preferred	<u>330112004</u>

Terminal for use in Sealed Application with 0.35-0.50mm ²	
MX150 Male Terminal for Mat-Sealed or Unsealed Connectors, Silver Plating, Grip Code M3, Left Reel Payoff, Contact Material Thickness 0.30mm, Preferred Terminal for use in Sealed Application with 0.35-0.50mm ²	<u>330113004</u>

This document was generated on Sep 14, 2025