



HONEYWELL PART NUMBER
4SX19-T
PRODUCT CODE VDF0876

REV	DOCUMENT	CHANGED BY	CHECK
6	0038447	SS 28MAR08	BLR



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188 ± .002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 SWITCH WILL WITHSTAND TEMPERATURE OF 400°F

RELEASE NO.	PR-6196
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ±		DRAWN	SPK	06FEB08	Honeywell			
OPERATING FORCE — — — — 5 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	06FEB08				
RELEASE FORCE— — — — — 1 OZ MIN		28 VOLTS DC RATING			0.030 0.015 0.005	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .002 MAX			SEA LEVEL	50,000 FT									
OVERTRAVEL — — — — — .004 MIN		INDUCTIVE	4 AMP	2.5 AMP		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		RESISTIVE	7 AMP	7 AMP					B	I	4SX19-T		6
		MAXIMUM INRUSH 24 AMP			THIRD ANGLE PROJECTION 		RASTER			SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1
		APPROVALS	KEMA, CE	7A 250V~ T125 5E4 						UL, CSA	7A 250 VAC  BRAND L7		