

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MATERIAL: NYLON 6


MATERIAL: POLYETHYLENE  $\triangle$

| PART NO. $\triangle$ | DIMENSIONS<br>A B |                  | WALL<br>THICKNESS              | WEIGHT<br>lbs / 100 ft<br>(g) |
|----------------------|-------------------|------------------|--------------------------------|-------------------------------|
| CLT25N-630 *         | 0.398<br>(10.10)  | 0.284<br>(7.20)  | 0.007 - 0.020<br>(0.18 - 0.51) | 0.81<br>(370.0)               |
| CLT35N-630 *         | 0.504<br>(12.79)  | 0.350<br>(8.88)  | 0.006 - 0.025<br>(0.15 - 0.64) | 1.28<br>(580.0)               |
| CLT38N-630 *         | 0.524<br>(13.30)  | 0.394<br>(9.99)  | 0.007 - 0.025<br>(0.18 - 0.64) | 1.47<br>(670.0)               |
| CLT50N-630 *         | 0.654<br>(16.60)  | 0.512<br>(12.99) | 0.007 - 0.020<br>(0.18 - 0.51) | 1.98<br>(900.0)               |
| CLT62N-630 *         | 0.847<br>(21.05)  | 0.664<br>(16.85) | 0.007 - 0.020<br>(0.18 - 0.51) | 2.39<br>(1085.0)              |
| CLT75N-630 *         | 0.941<br>(23.90)  | 0.767<br>(19.47) | 0.007 - 0.020<br>(0.18 - 0.51) | 2.75<br>(1250.0)              |
| CLT100N-630 *        | 1.103<br>(28.00)  | 0.912<br>(23.15) | 0.008 - 0.030<br>(0.20 - 0.76) | 3.70<br>(1680.0)              |
| CLT125N-630 *        | 1.536<br>(39.00)  | 1.278<br>(32.45) | 0.008 - 0.030<br>(0.20 - 0.76) | 6.03<br>(2740.0)              |
| CLT150N-630 *        | 1.851<br>(47.00)  | 1.575<br>(39.99) | 0.010 - 0.032<br>(0.25 - 0.81) | 7.39<br>(3360.0)              |
| CLT188N-630 *        | 2.194<br>(55.73)  | 1.849<br>(46.96) | 0.013 - 0.035<br>(0.33 - 0.89) | 11.20<br>(5088.0)             |



| PART NO. $\triangle$ | DIMENSIONS<br>A B |                  | WALL<br>THICKNESS              | WEIGHT<br>lbs / 100 ft<br>(g) |
|----------------------|-------------------|------------------|--------------------------------|-------------------------------|
| CLT25F- *            | 0.398<br>(10.10)  | 0.284<br>(7.20)  | 0.007 - 0.020<br>(0.18 - 0.51) | 0.75<br>(340.0)               |
| CLT35F- *            | 0.504<br>(12.79)  | 0.350<br>(8.88)  | 0.006 - 0.025<br>(0.15 - 0.64) | 1.12<br>(510.0)               |
| CLT38F- *            | 0.524<br>(13.30)  | 0.394<br>(9.99)  | 0.007 - 0.025<br>(0.18 - 0.64) | 1.38<br>(625.0)               |
| CLT50F- *            | 0.654<br>(16.60)  | 0.512<br>(12.99) | 0.007 - 0.020<br>(0.18 - 0.51) | 1.85<br>(840.0)               |
| CLT62F- *            | 0.847<br>(21.05)  | 0.664<br>(16.85) | 0.007 - 0.020<br>(0.18 - 0.51) | 2.29<br>(1040.0)              |
| CLT75F- *            | 0.941<br>(23.90)  | 0.767<br>(19.47) | 0.007 - 0.020<br>(0.18 - 0.51) | 2.64<br>(1200.0)              |
| CLT100F- *           | 1.103<br>(28.00)  | 0.912<br>(23.15) | 0.008 - 0.030<br>(0.20 - 0.76) | 3.52<br>(1600.0)              |
| CLT125F- *           | 1.536<br>(39.00)  | 1.278<br>(32.45) | 0.008 - 0.030<br>(0.20 - 0.76) | 5.77<br>(2620.0)              |
| CLT150F- *           | 1.851<br>(47.00)  | 1.575<br>(39.99) | 0.010 - 0.032<br>(0.25 - 0.81) | 6.16<br>(2800.0)              |
| CLT188F- *           | 2.194<br>(55.73)  | 1.849<br>(46.96) | 0.013 - 0.035<br>(0.33 - 0.89) | 9.10<br>(4127.3)              |

STANDARD PROFILE

DUAL RIB PROFILE  
(150 SIZE ONLY)



TUBING IS TO BE SLIT  
IN ONE PLACE DOWN ITS  
ENTIRE LENGTH



DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

$\triangle$  NOTES:

\* 1. SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL AND PART COLOR.

2. FOR ROLL SIZES LARGER THAN 10 FEET, SPLICES MAY OCCUR.

| 10  | 02.10.15 | BDK | VJS | RGR0 | E. ADDED DUAL RIB PROFILE AND DETAIL<br>F. REMOVED DENSITY FROM POLYETHYLENE                                                                                       | GB0222BP    |
|-----|----------|-----|-----|------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| 09  | 5/09/14  | BWG | VJS | JADE | $\triangle$ REVISED DIMENSIONS AND WEIGHTS, REMOVED PREVIOUS<br>REVISION BALLONS FOR CLARITY AND UPDATED<br>TITLE BORDER, ADDED * TO PART NUMBERS, REVISED NOTE 1. | GB0222BP/09 |
| REV | DATE     | BY  | CHK | APR  | DESCRIPTION                                                                                                                                                        | ECN         |

|                                                                                                                    |                 |            |               |                             |           |
|--------------------------------------------------------------------------------------------------------------------|-----------------|------------|---------------|-----------------------------|-----------|
| TITLE<br>CLT( ) N , CLT( ) F<br>SLIT CORRUGATED TUBING<br>CUSTOMER DRAWING $\triangle$                             |                 |            |               |                             |           |
| ITEM REVISION NAME<br>G03597BN/02                                                                                  |                 |            |               | <b>PANDUIT</b>              |           |
| DATASET FILE NAME<br>G03597BN_DC_GB0222BP_10/00A                                                                   |                 |            |               |                             |           |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]<br>.X ± .XXX ± 0.050 (1.27)<br>.XX ± ANGLES ± |                 |            |               | MATERIAL:<br>SEE ABOVE      |           |
| THIRD ANGLE<br>PROJECTION                                                                                          |                 |            |               | DRAWING NUMBER:<br>GB0222BP |           |
| DRAWN BY<br>CPE                                                                                                    | DATE<br>9-18-97 | CHK<br>VJS | SCALE<br>NONE | SHT 1 OF 1                  | SIZE<br>A |