

Representative Image

Catalog No. TY52315MX

Description: CABLE TIE 18LB 7IN UV BLK 2-PC DIST

UPC No 786210875453

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 170mm (6.7 Inches), Width of 2.54mm (0.10 Inch), Thickness of 1.1mm (0.043 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds)

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap

Dimensions

Width	0.09 in , 2.3 mm
Length	6.7 in , 170 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.06 to 1.26 in , 1.5 to 32 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC000046 Cable tie
Band width	2.3 mm

by ABB

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Band width	0.09 inch
Length belt/tape/tie	170 mm
Length belt/tape/tie	6.7 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	32 mm
Max. bundle diameter	1.26 inch
Min. holding force	80 N
Operation temperature	-60-+105 °C
Operation temperature	-76-+221 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Downloaded from Arrow.com.