

1634A Multi-Conductor - Type 1



For more Information
please call

1-800-Belden1

**General Description:**

IBM Type 1, 22 AWG solid BC conductors, non-plenum, flame-retardant foam polyethylene insulation, each pair individually Beldfoil® shielded, overall TC braid shield (65% coverage), rip cord, pvc jacket.

Usage (Overall)

Suitable Applications: Token Ring 4 & 16 Mbps, FDDI over copper and video

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
4	2	22	Solid	BC - Bare Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material
FRFPE - Flame Retardant Foam Polyethylene

Insulation Resistance: >16, 000 MOhms

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	65

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 7.518 x 10.947 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Orange
2	Red & Green

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

Bulk Cable Weight: 71.434 Kg/Km

Max. Recommended Pulling Tension:	369.201 N
Min. Bend Radius/Minor Axis:	76.200 mm
Min. Bend/Installation:	114.300 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
IEEE Specification:	IEEE802.5 Token Ring
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	Verified IBM Type 1
Customer Part Number Reference Specification:	IBM P/N: 4716748

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)

Surface Printing:	BELDEN 1634A CMG 75C 2PR22 SHIELDED (UL) E108998 C(UL)----ETL VERIFIED TO IBM SPECIFICATION 4716748
-------------------	--

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

150

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

27.8885

Maximum Capacitance Unbalance (pF/100 m):	150
---	-----

Nominal Velocity of Propagation:

VP (%)

78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

57.0894

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

7.5463

Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100 m)
4	2.2
16	4.5

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.3 Amps per conductor @ 25°C

Electrical Characteristics-Premise (Overall)**Premise****Minimum NEXT:**

Freq. (MHz)	NEXT (dB)
4	58
16	40

Notes (Overall)

Notes: IBM qualified Type 1 media cable for use in IBM cabling systems. For suffix "A" product see 9688

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1634A 0101000	1,000 FT	50.000 LB	BLACK	C Z	IBM TYPE1 STP CMG REEL

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 2 Revision Date: 01-18-2013

© 2019 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).