

DE2E3SA472MJ3BX02F



Applications

| | |
|-------------------------|---|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Consumer equipment, Industrial Equipment, Mobile Electronics, Medical equipment [GHF A/B/C] except for implant equipment, Automotive infotainment/comfort equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

Notices


X1/Y2 Class Certified Products、 Halogen-free Products、 Rated Voltage X1:300Vac(r.m.s.)/1500Vdc Y2:300Vac(r.m.s.)/1500Vdc

References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| B | Bulk(Bag) | 500 |


Appearance & Shape

| Mass (typ.) | |
|-------------|-------|
| 1 piece | 0.54g |



Attention
 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 2.This datasheet has only typical specifications because there is no space for detailed specifications.
 Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE2E3SA472MJ3BX02F



Specifications

| | |
|--|------------------------|
| L size or Outer diameter D | 10.0mm max. |
| T size | 5.0mm max. |
| Lead spacing F | 7.5±0.8mm |
| Lead diameter d | 0.6±0.05mm |
| Paint dripping e | Up to the end of crimp |
| Capacitance | 4700pF ±20% |
| Rated voltage | 300Vac(r.m.s.) |
| Temperature characteristics | E(JIS) |
| Capacitance change rate | +20/-55% |
| Temperature range of temperature characteristics | -25°C to 85°C |
| Operating Temperature Range | -40°C to 125°C |

Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE2E3SA472MJ3BX02F




Characteristic Data


The charts below may show another part number which shares its characteristics.




DE2E3SA472MJ3BX02F |Z| DC0V, 20degC



DE2E3SA472MJ3BX02F R DC0V, 20degC



DE2E3SA472MJ3BX02F C-DC bias capchange, 20.0




DE2E3SA472MJ3BX02F C-AC Voltage capchange, I


Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE2E3SA472MJ3BX02F



DE2E3SA472MJ3BX02F C-Temp. capchange, DC0V,



DE2E3SA472MJ3BX02F S21 DC0V, 20degC

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.