



+ CONNECTORS

SCREENED



✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

TE CONNECTIVITY (TE)
TXR21AZ00-1004AI

TXR21AZ00-1004AI
TE Internal Number: CW0956-000

[Not EU RoHS or ELV Compliant](#)
[Find Compliant Alternatives](#)

Adapter Angle **00**

Cable Diameter Range **32 – 51 mm [125 – 2 in]**

Adapter Entry Size **04**

TE Adapter Code **21**

Material **Aluminum**

Product Drawings

[Tinel-Lock Backshell](#)
PDF
English

CAD Files

[3D PDF](#)
PDF
3D

[Customer View Model](#)
2D_DXF.ZIP
English

[Customer View Model](#)
3D_IGS.ZIP
English

[Customer View Model](#)
3D_STP.ZIP
English

Catalog Pages/Data Sheets

[5-1654025-5_sec6_Adapters](#)
PDF
English

Product Specifications



Braid Termination Using A Tinel Lock Ring Installed Using A Resistance Heater.

PDF
English

PERFORMANCE SPECIFICATION Tinel-Lock Rings, Heat Recoverable For Braid Termination

PDF
English

ASSEMBLY GUIDE For Tinel -Lock Rings, Heat Recoverable For Braid Temination

PDF
English

General Information Package For Tinel-Lock Adapters

PDF
English

General Harness Repair Manual

PDF
English

Adapter Finish Specifications

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Adapter Angle	00
	Style	Tinel-Lock
	Termination Device Type	Side-Entry Tinel-Lock Ring, Tinel-Lock Ring
	Connector Shell Size	10
Configuration Features	Braid	36 Single
Body Features	Adapter Entry Size	04
	TE Adapter Code	21
	Material	Aluminum
	Adapter Plating Material	ZnNi per ASTM B841 over Suitable Underplated & Chromate
Dimensions	Cable Diameter Range	32 – 51 mm [125 – 2 in]
Industry Standards	Connector Detail Specification Number	MS3110, MS3111, MS3116, MS3120, MS3121, MS3126, MS3128
Other	Connector General Specification Number	MIL-DTL-26482 Series 1/Class E,F,J,P
Product Compliance	Statement of Compliance	
	PDF	

[VIEW ALL PRODUCT COMPLIANCE](#)