





Figure 1 is a schematic diagram of a multi-cavity mold. The mold is represented as a horizontal bar divided into four sections, labeled 1, 2, 3, and 4 from left to right. Each section contains a square cavity. Arrows point from the cavities in sections 2, 3, and 4 to a detail view labeled '5' and 'M'. This detail view is a triangle with the number '5' inside, and the text 'BLOCKED CAVITY' is written next to it. The text 'DETAIL M' is also present below the detail view.



DETAIL M	BLACK	35.56	4	1-282809-5
DETAIL M	GREEN	35.56	4	1-282809-4
-	GREEN	127.00	13	1-282809-3
-	GREEN	116.84	12	1-282809-2
-	GREEN	106.68	11	1-282809-1
-	GREEN	96.52	10	1-282809-0
-	GREEN	86.36	9	282809-9
-	GREEN	75.20	8	282809-8
-	GREEN	66.04	7	282809-7
-	GREEN	55.88	6	282809-6
-	GREEN	45.72	5	282809-5
-	GREEN	35.56	4	282809-4
-	GREEN	25.40	3	282809-3
-	GREEN	15.24	2	282809-2
MARKING	HOUSING COLOR	L	NO OF POSN	PART NUMBER

- | | | | | | |
|---|--|---|--|---|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DWN 23JUL2001
F. ZANOLINI
CHK 23JUL2001
D. BIEVENOUR
APVD 23JUL2001
D. BIEVENOUR | |  TE Connectivity | |
| DIMENSIONS:
mm | | TOLERANCES UNLESS
OTHERWISE SPECIFIED: | | NAME | |
|  | | 0 PLC ±.
1 PLC ±0.2
2 PLC ±0.25
3 PLC ±0.000
4 PLC ±0.0000
ANGLES ±2
FINISH | | PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
- | |
| MATERIAL | | CUSTOMER DRAWING | | SIZE
A2 | CAGE CODE
00779 |
| | | | | DRAWING NO
C-282809 | RESTRICTED TO
- |
| | | | | SCALE 4:1 | SHEET 1 OF 1 |