





DB UNLIMITED

Part Number:	DRAWN	6/14/2016
	CJ	
	CHECKED	6/14/2016
Description:	P.D.	J.S.
	APPROVED	6/14/2016
Dynamic Speaker		
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions	REVISION HISTORY			
Sound Pressure Level	92	dB (@ 10cm)	REV	DESCRIPTION	DATE	APPROVED
Resonant Frequency	350	Hz		Released from Engineering	2/8/2014	J.S.
Frequency Range	350 ~ 20,000	Hz	1	Updated to new template	6/14/2016	J.S.
Nominal Power	1	W	2	Corrected released from engineering information	11/7/2017	C.E.
Max. Power	1.5	W				
Impedance	8	Ω				
Cone Material	Mylar					
Mount Type	Flush Mount					
Storage Temperature	-30 ~ +60	°C				
Operating Temperature	-30 ~ +60	°C				
Weight	13.2	g				