








PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24A.PL00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24A.PL00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24A.PL00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24A.PL00LF

PERFORMANCE CLASS : 4 - 200 MATING CYCLES
PERFORMANCE CLASS : 6 - 500 MATING CYCLES



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6.0±0.15 mm.

GENERAL CHARACTERISTICS AND ROHS INFORMATION:
SEE DRAWING C01-8646-0000

mat'l. code SEE NOTE				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family D-SUB										
ltr	ecn no	dr	date	tolerances unless otherwise specified							title MALE CONNECTOR DELTA-D STRAIGHT - SOLDER TYPE									
H	ELX-I-21256	AB	2015-07-14	angles	linear	.0±0.1														
J	ELX-I-59406	DJ	2026-02-11			.00±0.1														
						0°±2°			.000±0.1											
				dr	LELEON		1992-09-10				dwg no					sheet 1 of 4			size	
				enqr	DIPU JOSEPH		2026-02-11				C01-8646-0096					A3				
				chr	GREGAR M		2026-02-11													
				appd	ALEX BABU		2026-02-11				type Product Customer Drawing									
sheet index		revision		J																
		sheet		1																