


© 2025 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED AS PER ECN-25-351332	28OCT2025	PSK	J.M





Suggested PCB Footprint



Note: Remove all sharp edges, burrs & pip

ENVIRONMENTAL PARAMETER	
TEMPERATURE RANGE	−55 ℃~+125 ℃

MATERIALS AND PLATING UNIT: MICRO-INCHES	
MATERIALS	PLATING
BRASS ALLOY	GOLD10u"/NICKEL 50u"

TE PART NUMBER	DIM=A	TE DESCRIPTION
2511418-1	1.40	CONTACT PAD, 2.99D X 1.40H, GOLD
2511418-2	1.91	CONTACT PAD, 2.99D X 1.91H, GOLD

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.2
2 PLC	± 0.1
3 PLC	± 0.05
4 PLC	± –
ANGLES	± –

MATERIAL: SEE TABLE

FINISH: SEE TABLE

DWN PRATHAP SK 20JUN2025

CHK MADHAN S 20JUN2025

APVD JAGRUTI M 20JUN2025

PRODUCT SPEC: 108-162165

APPLICATION SPEC: –

WEIGHT: 0

TE Connectivity Ltd.

NAME: – CONTACT PAD 2.99D GOLD –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2511418	–

CUSTOMER DRAWING

SCALE 1:1 SHEET 1 OF 2 REV A1

2511418

1471-9 (1/15)


Downloaded from Arrow.com.

© 2025 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—

NOTES :
1.PRIMARY PACKING: 2500 PCS/DISH(2500PCS)

2.OUTER PACKING: 4 DISH/CARTON(10000PCS)



4 dish



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRATHAP SK 20JUN2025	TE Connectivity Ltd.
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –	CHK MADHAN S 20JUN2025	NAME – CONTACT PAD 2.99D GOLD –
		APVD JAGRUTI M 20JUN2025	
		PRODUCT SPEC 108-162165	
		APPLICATION SPEC —	SIZE A2 / CAGE CODE 00779 / DRAWING NO C-2511418 / RESTRICTED TO —
MATERIAL –	FINISH –	WEIGHT —	
		CUSTOMER DRAWING	SCALE 1:1 / SHEET 2 OF 2 / REV A1

2511418

Downloaded from Arrow.com.