

© 2026 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C7	PART STATUS CHANGE TO DISCONTINUNACE	13JUL2026	NS	PS




1. MATERIALS AND FINISH
   HOUSING: PA 6-6, UL 94-V0, COLOR - SEE TABLE.
   CLAMP: BRASS, NICKEL PLATED.
   TERMINAL: BRASS, SEE TABLE.
   CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
4. WIRE SIZE RANGE
   12 - 30 AWG
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC., FILE N° E60677.
6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
7. NOT CUMULATIVE TOLERANCE.




282900-3 AS SHOWN





RECOMMENDED PC BOARD LAYOUT



	BLACK	MATTE TIN	25	5	1-282900-6
OBSOLETE	BLACK	0.76um GOLD	25	5	1-282900-5
	GREEN	TIN	40	8	282900-8
OBSOLETE	GREEN	0.76um GOLD	25	5	282900-5
	GREEN	TIN	15	3	282900-3
	GREEN	TIN	10	2	282900-2
	COLOR	**PLATING**	**DIM.A**	**N° OF POS.**	**PART NUMBER**

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±.3
2 PLC ±.25
3 PLC ±-
4 PLC ±-
ANGLES ±2

MATERIAL 1

FINISH 1

DWN E. ZANOLINI 07NOV2001
CHK D. BIEVENOUR 07NOV2001
APVD D. BIEVENOUR 07NOV2001
PRODUCT SPEC 108-20166
APPLICATION SPEC 114-20079
WEIGHT -

TE Connectivity

NAME
TERMINAL BLOCK, PCB MOUNT
2ND LEVEL
STACKING W/INTERLOCK, 5mm. PITCH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-282900	-

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV C7

1470-19 (3/13)

Downloaded from Arrow.com.