

Part Number : 1202530563
Product Description : Contrinex Inductive Sensor, M12 Fully Stainless Steel, 10mm Operating Distance, Non-embeddable, PNP, NO, 2m 3-wire PUR Cable, 50mm Housing Length
Series Number : 120253
Status : Obsolete
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : DW-AD-713-M12

Obsolete

Documents and Resources

Specifications

1202530561-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M12 Fully Stainless Steel, 10mm Operating Distance, Non-embeddable, PNP, NO, 2m 3-wire PUR Cable, 50mm Housing Length
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130069880

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 400 Hz

Physical

Connection	Cable (PUR 2m, 3-wire)
Length	50mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Non-embeddable
Operating Distance	10mm
Output	NO
Sensor Housing Size	M12
Temperature Range - Operating	-25° to +85°C

Obsolete

Downloaded from Arrow.com.

This document was generated on Oct 07, 2026

Obsolete

Downloaded from Arrow.com.