

Search within category

GO

BUY NOW

DESIGN / INSTALL



P6-56RHT6-E

High Temperature Ring Terminal, 6 AWG, 5/16" stud size, non-insulated.

Specs	Packaging Details	Tools	Documents	★ Add to Favorites	🛒 Add to BOM
Stud Size	5/16"				
Wire Range	6 AWG				
Wire Range (mm²)	16				
Barrel Configuration	Standard				
Barrel Type	High Temperature, Brazed Seam				
Base Material	Copper				
Insulation	Non-Insulated				
Panduit Color Code	Metallic				
Plating Type	Nickel				
Part Number Series	P-RHT6				
Clearance	0.51				
Clearance (mm)	13.0				
Length (In.)	1.33				
Length (mm)	33.8				
Stock	0.05				
Stock (mm)	1.1				
Width (In.)	0.62				
Width (mm)	15.8				
Wire Strip Length (In.)	7/16" (.4375)				
Wire Strip Length (mm)	11.11				
Flammability Rating	N/A				
Max. Voltage Rating	2000 V				
Temperature Rating	650 Degrees Fahrenheit (343 Degrees Celsius)				
CA-800/EZ Series Crimp Die	—				
CA9 Series Crimp Die	—				
Tool	CT-2600, CD-2600-P6				
CSA Certified	C22.2 No. 65				
Mil. Std. Part Number	—				
UL Listed	UL 486A - UL 486B				
Packaging Type	Bottle				

Part Features

• Ring tongue design assures a secure connection in high vibration applications • Nickel plated copper for temperatures up to 650°F (343°C) • Internal barrel serrations assure good wire contact and maximum tensile strength

RoHS Compliancy Status	Compliant
Min. Order Qty.	20

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)