

# Product data sheet

Specifications



## APC NetShelter Basic Rack PDU, 0U, 15A, 100/120V, 14 NEMA 5-15 outlets

AP9567

### Overview

<b>Presentation</b>	APC Basic Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events. Packaging Includes PDU, Installation guide, Rack Mounting brackets, Toolless Mounting Kit.
---------------------	--

<b>Lead time</b>	Usually in Stock
------------------	------------------

### Main

<b>Colour</b>	Black
<b>Product or component type</b>	PDU
<b>PDU type</b>	Basic
<b>Cord length</b>	3.7 m
<b>Number of cables</b>	1
<b>Provided equipment</b>	Installation guide Rack mounting brackets Toolless mounting kit

### Complementary

<b>Input Voltage</b>	100 V 120 V
<b>Height</b>	61 cm
<b>Width</b>	4.4 cm
<b>Output Voltage</b>	100 V 120 V
<b>Depth</b>	4.4 cm
<b>Product weight</b>	2.18 kg
<b>Mounting location</b>	Side
<b>Mounting preference</b>	No preference
<b>Input Plug Type</b>	NEMA 5-15P
<b>Mounting mode</b>	Rack-mounted
<b>Rack units</b>	0U
<b>Mounting position</b>	Vertical
<b>[In] rated current</b>	12 A
<b>Permissible voltage</b>	100...125 V

Input current limits	15 A
Load capacity	1400 VA
Network frequency	50/60 Hz
Outlet type and quantity	14 NEMA 5-15R

## Environment

Product certifications	cUL listed METI Denan UL listed
Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...15240 m

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	64.8 cm
Package 1 Width	15.2 cm
Package 1 Length	17.8 cm
Package 1 Weight	2.92 kg

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint **55**

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

[EU RoHS Directive](#) **Compliant**

REACH Regulation [REACH Declaration](#)

California proposition 65 **WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](#)**

Halogen-free status **Product contains halogen above thresholds**

### Energy efficiency

Energy Efficiency Optimized **Energy efficient product**

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back **No**

WEEE Label **The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**

Image of product / Alternate images

Alternative

---



