

**Part Number :** [918139102](#)

**Product Description :** 5.08mm Pitch KK Crimp Housing, 2 Circuits, White, with Ramp, Glow-Wire Capable

**Series Number :** 91813

**Status :** Not Recommended For New Design

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[30010001-PK-000.pdf](#)


### Specifications

[PS-99020-0087-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

Status	Not Recommended For New Design
Category	Connector Housings
Series	91813
Description	5.08mm Pitch KK Crimp Housing, 2 Circuits, White, with Ramp, Glow-Wire Capable
Application	Power, Wire-to-Board
Comments	This Molex product is manufactured from material that has the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12 and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable

	product end-use standard(s). If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.
Product Name	KK 508
UPC	800756784632

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	2
Color - Resin	Natural (White)
Gender	Receptacle
Glow-Wire Capable	Yes
Material - Resin	Nylon
Net Weight	0.624/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	See Product Specification

---

### Mates With / Use With

#### Mates with Part(s)

Description	Part Number
KK 508 Vertical Headers	<u>173083</u>

**Use with Part(s)**

Description	Part Number
KK 396 Female Crimp Terminals	<u>2478</u>
KK 396 Female Crimp Terminals	<u>2578</u>
KK Female Crimp Terminals	<u>2878</u>

---

This document was generated on Apr 13, 2026