


HONEYWELL
PART NUMBER

111SM117-H2

PRODUCT CODE
TYJ5925

REV	DOCUMENT	CHANGED BY	CHECK
6	0039671	KVB 08MAY08	BLR

STAINLESS STEEL LEAF



- NOTES
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $.087$ MAX DIA ON $.375 \pm .002$ CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
 - 4 CHARACTERISTICS TAKEN AT POINT "A"

RELEASE NO. PR - 19021

REPLACES X93259 - SM

CHARACTERISTICS 4

OPERATING FORCE - - - - 8 OZ MAX

RELEASE FORCE - - - - 2 OZ MIN

DIFFERENTIAL TRAVEL - - .0045 MAX

OVERTRAVEL - - - - .013 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT S P D T			
30 VOLTS DC RATING			
		SEA LEVEL	50,000 FT
INDUCTIVE		3 AMP	2.5 AMP
RESISTIVE		5 AMP	5 AMP
MAXIMUM INRUSH 24 AMP			
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4	 
	UL, CSA	5A, <u>250</u> VAC	  BRAND L4

DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACE	X	±	-
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	-
ANGLES		±	-
THIRD ANGLE PROJECTION			

DRAWN	VK	26 OCT 07
CHECK	RJ	26 OCT 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

HoneywellTITLE
SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	111SM117-H2	6
SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1