



HONEYWELL PART NUMBER
1SM46-T
PRODUCT CODE TWA4660

REV	DOCUMENT	CHANGED BY	CHECK
12	0038442	SSK 31MAR08	BLR




PLASTIC PLUNGER.



NOTES

- 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $.087$ MAX. DIA. ON $.375 \pm .002$ CENTERS.
- 2- TERMINALS ARE PLATED FOR SOLDERING.
- 3- NORMALLY OPEN MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.	-
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	VK	10 DEC 07	Honeywell			
OPERATING FORCE — — 3 - 5 OZ		CONTACT ARRANGEMENT SPDT					CHECK	RJ	10 DEC 07				
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			SIZE B TYPE I DRAWING NAME 1SM46-T REV 12			
DIFFERENTIAL TRAVEL— — — .004 MAX													
OVERTRAVEL — — — — — .005 MIN													
		INDUCTIVE					INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY						
		RESISTIVE											
		MAXIMUM INRUSH 2 AMP											
							RASTER			SCALE - WEIGHT .006 LB MAX SHEET 1 OF 1			

