




RAYCHEM

TE Internal #: 648906-000

Right Angle, 3, 10, Adhesive Precoat Adhesive Requirement, -55 – 135 °C [-67 – 275 °F], 42, Heat Shrink Boots

[View on TE.com >](#)

Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Boots



Body Orientation: **Right Angle**

Material Code: **3**

Material Systems Code: **10**

Adhesive Requirement: **Adhesive Precoat**

Operating Temperature Range: **-55 – 135 °C [-67 – 275 °F]**

**Features**

**Configuration Features**

Adhesive Requirement	Adhesive Precoat
----------------------	------------------

**Body Features**

Primary Product Material	Semi rigid Modified Polyolefin
Material Code	3
Material Systems Code	10

**Housing Features**

Body Orientation	Right Angle
------------------	-------------

**Usage Conditions**

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

**Other**

Adhesive Code	42
---------------	----

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)











Candidate List Declared Against: JUNE 2024 (241)  
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought

 <p>TE Part #5172068-1 16P FEMALE HSG ASSY DROWER</p>	 <p>TE Part #925486-1 MOD. IV SNAP-IN HSG 96 POS.</p>	 <p>TE Part #102241-4 06 MODIV HSG COMP SR .100 POL</p>	 <p>TE Part #87077-2 MOD IV KEYING PLUG</p>
 <p>TE Part #102241-2 04 MODIV HG COMP SR .100 POL</p>	 <p>TE Part #176271-1 AMP UNIVERSAL POWER PLUG 2P</p>	 <p>TE Part #1-87631-3 18 MODIV HSG COMP DR .100 POL</p>	 <p>TE Part #5070052031 RNF-100-3/16-X-STK</p>
 <p>TE Part #NB19534001 RNF-100-3/16-RD-SP</p>	 <p>TE Part #CW2824-000 R85049/128-7</p>		



## Documents

### Product Drawings

[234A032-3/42-0](#)

English

---

### Datasheets & Catalog Pages

[1654025\\_Sec4\\_-3](#)

English

[Raychem Molded Parts Visual Guide](#)

English

---

### Product Specifications

[Product Specification](#)

English