

- Wide 2:1 input voltage range
- Compact SIP-6 package
- Fully regulated outputs
- Cost optimised design
- No minimum load required
- Continuous short circuit protection
- Temperature range -40°C to $+95^{\circ}\text{C}$
- I/O isolation 1500 VDC
- 3-year product warranty



UL 62368-1 IEC 62368-1

The TMR 1 series is a family of isolated 1 W DC/DC converter modules with regulated output, featuring wide 2:1 input voltage ranges. These products come in a compact SIP-6 package with small footprint.

An excellent efficiency allows -40°C to $+95^{\circ}\text{C}$ operation temperature. Further features continuous short circuit protection. The compact dimensions and cost optimised design make this converters an ideal solution for applications in communication equipment, instrumentation and industrial electronics.

Models

Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
TMR 1-0511	4.5 - 9 VDC (5 VDC nom.)	5 VDC	200 mA	-12 VDC -15 VDC	42 mA 33 mA	76 %
TMR 1-0512		12 VDC	83 mA			77 %
TMR 1-0513		15 VDC	67 mA			79 %
TMR 1-0515		24 VDC	42 mA			76 %
TMR 1-0522		+12 VDC	42 mA			77 %
TMR 1-0523		+15 VDC	33 mA			78 %
TMR 1-1211	9 - 18 VDC (12 VDC nom.)	5 VDC	200 mA	-12 VDC -15 VDC	42 mA 33 mA	77 %
TMR 1-1212		12 VDC	83 mA			77 %
TMR 1-1213		15 VDC	67 mA			80 %
TMR 1-1215		24 VDC	42 mA			77 %
TMR 1-1222		+12 VDC	42 mA			79 %
TMR 1-1223		+15 VDC	33 mA			78 %
TMR 1-2411	18 - 36 VDC (24 VDC nom.)	5 VDC	200 mA	-12 VDC -15 VDC	42 mA 33 mA	77 %
TMR 1-2412		12 VDC	83 mA			80 %
TMR 1-2413		15 VDC	67 mA			80 %
TMR 1-2415		24 VDC	42 mA			77 %
TMR 1-2422		+12 VDC	42 mA			80 %
TMR 1-2423		+15 VDC	33 mA			80 %
TMR 1-4811	36 - 75 VDC (48 VDC nom.)	5 VDC	200 mA	-12 VDC -15 VDC	42 mA 33 mA	77 %
TMR 1-4812		12 VDC	83 mA			78 %
TMR 1-4813		15 VDC	67 mA			78 %
TMR 1-4815		24 VDC	42 mA			76 %
TMR 1-4822		+12 VDC	42 mA			79 %
TMR 1-4823		+15 VDC	33 mA			79 %

Input Specifications

Input Current	- At no load	5 Vin models: 40 mA typ. 12 Vin models: 20 mA typ. 24 Vin models: 10 mA typ. 48 Vin models: 7 mA typ.
Surge Voltage		5 Vin models: 15 VDC max. (1 s max.) 12 Vin models: 25 VDC max. (1 s max.) 24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.)
Under Voltage Lockout		5 Vin models: 4 VDC max. 12 Vin models: 8.5 VDC max. 24 Vin models: 17.5 VDC max. 48 Vin models: 35.5 VDC max. (Long term operation at undervoltage will damage the converter)
Reflected Ripple Current		5 Vin models: 80 mAp-p typ. 12 Vin models: 40 mAp-p typ. 24 Vin models: 30 mAp-p typ. 48 Vin models: 20 mAp-p typ.
Recommended Input Fuse		5 Vin models: 500 mA (slow blow) 12 Vin models: 250 mA (slow blow) 24 Vin models: 120 mA (slow blow) 48 Vin models: 60 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)

Output Specifications

Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax) - Load Variation (10 - 90%)	single output models: 0.2% max. dual output models: 0.2% max. single output models: 0.5% max. dual output models: 0.8% max. (Output 1) 0.8% max. (Output 2)
Ripple and Noise	- 20 MHz Bandwidth	110 mVp-p max.
Capacitive Load	- single output - dual output	5 Vout models: 1'680 µF max. 12 Vout models: 820 µF max. 15 Vout models: 680 µF max. 24 Vout models: 470 µF max. 12 / -12 Vout models: 470 / 470 µF max. 15 / -15 Vout models: 330 / 330 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Short Circuit Protection		Automatic recovery
Overload Protection		Foldback Mode
Output Current Limitation		120% min. of Iout max. 130% typ. of Iout max.
Transient Response	- Response Deviation - Response Time	5% max. (25% Load Step) 250 µs typ. (25% Load Step)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Safety Specifications

Standards	- IT / Multimedia Equipment	CSA-C22.2, No. 60950-1 EN 60950-1 EN 62368-1 IEC 60950-1 IEC 62368-1 UL 60950-1 UL 62368-1 www.tracopower.com/tmr1-safety-cert/
	- Certification Documents	
Energy Source	- Output, acc. to 62368-1	ES1
Power Source	- Output, acc. to 62368-1	PS3
Pollution Degree		PD 2
Over Voltage Category		Not mains connected

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 55032 class A (with external filter) FCC 47 Part 15 class A (with external filter) External filter proposal: www.tracopower.com/tmr1-emc-filter/
-----------------	-----------------------	--

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature - Case Temperature - Storage Temperature	-40°C to +95°C +105°C max. -55°C to +125°C
Power Derating	- High Temperature	5.0 %/K above 85°C See application note: www.tracopower.com/tmr1-cc/
Cooling System		Natural convection (20 LFM)
Altitude During Operation		6'000 m max.
Regulator Topology		RCC Converter
Switching Frequency		220 kHz typ. (PFM)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	1'500 VDC
Isolation Resistance	- Input to Output, 500 VDC	1'000 MΩ min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	50 pF max.
Reliability	- Calculated MTBF	2'800'000 h (MIL-HDBK-217F, ground benign)
Washing Process		According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Housing Material		Non-conductive Plastic (UL 94 V-0 rated)
Potting Material		Silicone (UL 94 V-0 rated)
Pin Material		Nickel-Iron (Alloy 42)
Pin Foundation Plating		Nickel (1 µm min.)
Pin Surface Plating		Tin (3 - 5 µm), matte
Housing Type		Plastic Case
Mounting Type		PCB Mount
Connection Type		THD (Through-Hole Device)
Footprint Type		SIP6
Soldering Profile		Lead-Free Wave Soldering 260°C / 10 s max.
Weight		3.1 g

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance - REACH Declaration

www.tracopower.com/info/reach-declaration.pdf

- RoHS Declaration

REACH SVHC list compliant

REACH Annex XVII compliant

www.tracopower.com/info/rohs-declaration.pdf

Exemptions: 7(a)

(RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).)

- SCIP Reference Number

6e8a01b2-0222-4a2e-869a-fb9db21dc6f0

Additional Information

Supporting Documents

www.tracopower.com/overview/tmr1

Frequently Asked Questions

www.tracopower.com/glossary-faq



Glossary

www.tracopower.com/info/glossary.pdf


Service Portal

www.tracoserviceportal.com

Outline Dimensions



Dimensions in mm (inch)
Tolerances: x.x±0.5 (x.xx±0.02)
x.xx±0.25 (x.xx±0.01)
Pin tolerances: ±0.05 (±0.002)



Pinout

Pin	Single Output	Dual Output
1	–Vin (GND)	–Vin (GND)
2	+Vin (Vcc)	+Vin (Vcc)
4	+Vout	+Vout
5	No pin	Common
6	–Vout	–Vout

Avoid routing PCB traces under the converter.