




**Part Number :** [351500404](#)

**Product Description :** VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Blue

**Series Number :** 35150

**Status :** Not Recommended For New Design

**Product Category :** Connector Housings



---

## Documents and Resources

### Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)


[PK-35150-004-001.pdf](#)

[PS-35150-003-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Not Recommended For New Design
Category	Connector Housings
Series	35150
Description	VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Blue
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	756054256626

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	4
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.120/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
VersaBlade Hybrid Plug Housings	<a href="#">35151</a>

### Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	<a href="#">351500290</a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	<a href="#">351500292</a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	<a href="#">351500293</a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue	<a href="#">351500294</a>
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<a href="#">2270288400</a>
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	<a href="#">2270298400</a>
VersaBlade Male Crimp Terminals	<a href="#">35745</a>
VersaBlade Female Crimp Terminals	<a href="#">35746</a>
VersaBlade Male Crimp Terminals	<a href="#">35747</a>

VersaBlade Female Crimp Terminals	<u>35748</u>
--------------------------------------	--------------

---

This document was generated on Apr 13, 2026