









15 POSITIONS



SPECIFICATIONS	
CURRENT RATING:	3A
WITHSTANDING VOLTAGE:	500VAC FOR 1 MIN.
INSULATION RESISTANCE:	500 MΩ MIN.
CONTACT RESISTANCE:	30 mΩ MAX.
TEMPERATURE RANGE:	-55°C TO 105°C
INSULATOR MATERIAL:	PBT+30% G.F.
INSULATOR COLOR:	BLACK
SHELL MATERIAL:	STEEL
CONTACT MATERIAL:	BRASS
CONTACT PLATING:	GOLD FLASH
HARDWARE MATERIAL:	BRASS

REVISIONS

REV.	DESCRIPTION	DATE	BY
1	ORIGINAL	DRAWN DATE	

SERIES	MHHDR - RIGHT-ANGLE P.C.TAIL
POSITIONS	15 - 15 POSITIONS 26 - 26 POSITIONS 44 - 44 POSITIONS 62 - 62 POSITIONS
GENDER	M - MALE
SHELL PLATING	N - NICKEL PLATING
CONTACT TYPE	S - STAMPED
HARDWARE OPTIONS	A - #4-40 THREADED HOLE, NI PLATED, BOARDLOCK, TIN PLATED B - #4-40 THREADED STANDOFF, NI PLATING, BOARDLOCK, TIN PLATED C - #4-40 THREADED HOLE, NI PLATED, L GROUND STRAPS, TIN PLATED
CONTACT PLATING	1 - GOLD FLASH

POSITIONS	A	B	C	D
15	30.81	24.99	16.92	2.29
26	39.14	33.32	25.25	2.29
44	53.04	47.04	38.96	2.29
62	69.32	63.50	55.42	2.41

MH
CONNECTORS

MH CONNECTORS
LTD.

RoHS
COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC, AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN BY	V.K.	MHHDR SERIES, D-SUB, HIGH DENSITY, RIGHT-ANGLE P.C.TAIL, MALE			
DRAWN DATE	11/28/2025				
CHECKED BY	R.S.M.	PART NUMBER MHHDR-XXMNS-X1			
CHECK DATE	11/29/2025				
TOLERANCES	ALL DIMENSIONS AND TOLERANCES IN MM	MATERIAL	SIZE	A	REVISION
.X	±0.30				1
.XX	±0.25				
.XXX	±0.10	SCALE	1:1	SHEET	1 OF 1