

M12-CON-1.0-AWG22-18/0,33-0,82mm²-M



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 21 01 100 9981 |
| Specification | M12-CON-1.0-AWG22-18/0,33-0,82mm ² -M |
| HARTING eCatalogue | https://harting.com/21011009981 |

Identification

| | |
|-----------------|-------------------------|
| Category | Contacts |
| Series | Circular connectors M12 |
| Identification | Power |
| Type of contact | Crimp contact |

Version

| | |
|-----------------------|-------------------|
| Termination method | Crimp termination |
| Gender | Male |
| Manufacturing process | Turned contacts |

Technical characteristics

| | |
|-------------------------------|-------------------------------|
| Conductor cross-section | 0.33 ... 0.82 mm ² |
| Conductor cross-section [AWG] | AWG 22 ... AWG 18 |
| Performance level | 1 |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Gold plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 100 |
| Net weight | 0.002 g |
| Country of origin | Switzerland |
| European customs tariff number | 85366990 |
| GTIN | 5713140229396 |
| eCl@ss | 27440204 Contact for industrial connectors |
| ETIM | EC000796 |
| UNSPSC 24.0 | 39121522 |