

 [Live Product Chat](#)



✓ Active

 [Add to Part List](#)

 [View 3D PDF](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Receptacle
- HV-100
- Number of Positions = 11
- Number of Rows = Single
- Standard Profile

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings: • HV 100 VERTICAL CONNECTOR (TIF, German) Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: (CAD Format & Compression Information) • 2D Drawing (DXF, Version C1) • 3D Model (IGES, Version C1) • 3D Model (STEP, Version C1) List all Documents	Additional Information: • Product Line Information Related Products: • Tooling
---	--

Product Type Features: • Product Type = Receptacle • Connector Series = HV-100 • Number of Positions = 11 • Profile = Standard • Mount Angle = Vertical • Mounting Pattern (mm [in]) = 2.54 [.100] • Sealed = No • Holddown Feature = Without • PCB Retention Feature = Yes • Closed Entry = With • Board Standoff = With Mechanical Attachment: • Stackable = Yes Termination Related Features: • Termination Method = Through Hole • Termination (Solder) Post Length (mm [in]) = 3.10 [0.122] • Solder Tail Contact Plating = Tin Body Related Features: • Number of Rows = Single • Connector Height (mm [in]) = 7.00 [0.276] • Centerline, Matrix (mm [in]) = 2.54 [.100] • PCB Retention Method = Retention Solder Tails • Closed Bottom = With	Contact Related Features: • Contact Mating Area Plating Material = Gold (30) • Contact Material = Phosphor Bronze Housing Related Features: • Housing Entry Style = Top • Housing Material = Polyester GV • Housing Flammability Rating = UL 94V-0 • Housing Color = Green Industry Standards: • Government/Industry Qualification = No • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant Other: • Brand = AMP
---	---